



# 18VX2 LAWNMOWER 38CM LXT DLM382CT2

DLM382 is 380mm push type cordless lawn mower with plastic deck, and powered by two 18V LXT Li-Ion batteries in series.

Recommended for lawns up to 560m<sup>2</sup>



## TECHNICAL SPECIFICATIONS

|                          |                          |
|--------------------------|--------------------------|
| Battery Type             | Li-ion                   |
| Voltage                  | 36 (18v x2) v            |
| Battery Quantity (5.0ah) | 2                        |
| Noise sound pressure     | 81 dB(A)                 |
| Noise sound power        | 91 dB(A)                 |
| Noise K factor           | 3 dB(A)                  |
| Blade type               | Rotary type 2 tooth      |
| Cutting diameter         | 380 mm                   |
| Cutting heights          | 13 / 20-75 Levels/<br>mm |
| Collection box           | 40 litres                |
| No Load Speed            | 3700 rpm                 |
| Vibration K factor       | 1.5 m/sec <sup>2</sup>   |
| Vibration no load        | 2.5 m/sec <sup>2</sup>   |
| Net weight               | 16.2 – 16.9 kg           |

## USER BENEFITS

- Electric brake
- Soft start
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Single lever cutting height adjustment
- Grass box with grass level indicator
- Rubberised handle bar
- Low noise and vibration

[Link to product - makitauk.com](https://www.makita.co.uk)



# RELATED PRODUCTS

(Recon

STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



OTHER