



18Vx2 Pressure Washer BL LXT

DHW080ZK

DHW080 is a cordless high pressure washer powered by two 18V LXT batteries in series, featuring transportability and high washing performance enough to clean cars or agricultural machinery



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	36 (18Vx2) v
Temperature	0 - 40 °
Tank Capacity	50 litres
Noise sound pressure	70.9 dB(A)
Noise K factor	3.6 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	6.4 - 7.7 kg
Pump Speed (Hi/Lo Pressure)	3,450 / 2,390 rpm
Regular Pressure (Hi/Lo setting)	55 / 30 bar
Max Permissible Pressure	80 bar
Regular Flow (Hi/Lo Pressure)	330 / 240 l/hr
Max Water Flow	380 l/hr

USER BENEFITS

- Brushless motor
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Step-less pressure adjustment close at hand: Jet pressure can be adjusted simply by turning the nozzle of the vario spray lance
- High/Low 2-pressure selection
- Self-priming function (with a max suction height of 1 m) - Water can be supplied not only from a faucet but also from a tank or bucket using self-suction hose set.
- Storage space for attachment
- Hook for shoulder belt
- Up to 34mins run time with 2x 6.0Ah batteries
- Wet Guard: Excellent water-resistant performance allows to operate the machine even when it is wet with water as long as the battery cover is closed
- Supplied with a storage case that can also be used as a water tank with a capacity of approx. 50 litres

[Link to product - makitauk.com](https://www.makita.co.uk)



RELATED PRODUCTS

(Recon

■ OTHER