



40Vmax Brush Cutter BL XGT

UR002GD201

UR002G is a cordless Brush Cutter powered by 40Vmax XGT Li-ion battery



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Spindle Size	M10 x 1.25mm Left
Noise sound pressure	72.2 dB(A)
Net weight	4.6 – 5.3 kg
Noise K factor	2.2 dB(A)
Vibration K factor	1.5 m/sec ²
No Load Speed (Med)	5300 rpm
Voltage	40 v
Battery Quantity (2.5Ah)	2
Noise sound power	89.7 dB(A)
Cutting diameter	350 mm
No Load Speed (Hi)	6500 rpm
No Load Speed (Lo)	3500 rpm
Vibration: Nylon Cutting Head	2.5 m/sec ²

USER BENEFITS

- Active Feedback Sensing Technology (AFT): Shuts down the tool if the rotation speed suddenly slows down
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Brushless motor
- Electric brake
- Soft start feature.
- Constant speed control
- Reverse switch for easy removal of grass clippings stuck.
- Electronic 3-speed (Hi/Med/Lo)
- Small protector for better view of cutting area
- Extremely low noise
- IPX4 level water resistant
- Ergonomic handle bar of off-set design

Link to product - makitauk.com



RELATED PRODUCTS

(Recom

STANDARD ACCESSORIES

191B36-3
BL4025 XGT 2.5AH 40v Max Li-ion



191C10-7
ADP10 XGT TO LXT CHARGER



191E08-6
DC40RA FAST CHARGER SET



OTHER