

Dynabook Satellite Pro C40-G-111 (A1PYS26E114P)
Dynabook Satellite Pro C40-G-111 - Core i3 10110U / 2.1 GHz - Win 10 Home 64-bit - 8 GB RAM - 256 GB SSD - 14" 1366 x 768 (HD) - UHD Graphics - Wi-Fi 5,Bluetooth - dark blue,tile black (keyboard)



This laptop offers all the tools you need for a productive work or study day,yet is effortlessly portable and budget-friendly. Multitasking is made easy thanks to a powerful processor,super-fast DDR4 RAM and SSD storage,while the USB Type-C port provides one-click connection to your most-used peripherals.

Key Selling Points

- Powerful processor
- Non-reflective display
- Huge memory
- Advanced graphics
- Long-lasting battery

Product Features

Maximum productivity
Power through your work or study day with a versatile and highly-capable device. Powerful processors,huge DDR4 RAM memory and lag-free SSD storage mean it's equipped to exceed your demands.

Designed for life on the move
The Satellite Pro C40 is dressed to impress with contemporary design. Weighing just 1.55kg and measuring in at a slender 18.9mm,it's the perfect companion for life on-the-go. It also boasts long battery life,so you can enjoy a full work or study day away from mains power. Meanwhile,its narrow-bezel design and non-glare screen deliver an immersive experience,and its large keyboard provides comfort and control throughout the day.

Get connected wherever you go
Work or learn from anywhere - the Satellite Pro C40 is equipped to keep you connected. Stream,study or browse with reliable Wi-Fi,Bluetooth and Gigabit-LAN. Built-in USB Type-C lets you charge,connect,display and transfer data through a single port. What's more,a full-size HDMI port makes big-screen presentations easy,and a microSD card reader lets you access portable storage whenever you need to.

Make communication simple
Never miss a moment with the Satellite Pro C40. The device's Windows Hello-ready HD webcam,stereo speakers and Cortana-enabled microphone make staying in touch with customers,colleagues and peers effortless. Need to connect a headset? Simply pair via Bluetooth or plug in through the mic/headphone combination slot.

Secure down to its core
Thanks to the enterprise-grade encryption provided by firmware-based Trusted Platform Module (TPM) 2.0,the Satellite Pro C40 is equipped to keep your data out of the wrong hands. User and admin password capabilities prevent unsolicited access,and a Kensington lock slot gives extra peace of mind if you need to leave your device unattended.

The hygiene factor
It is important to keep the workspace as hygienic as possible. With that in mind,Dynabook has added an antibacterial coating to all the Satellite Pro C40's painted surfaces.

Main Specifications

| | |
|---------------------|--|
| Product Description | Dynabook Satellite Pro C40-G-111 - 14"- Core i3 10110U - 8 GB RAM - 256 GB SSD |
| Product Type | Notebook |
| Operating System | Win 10 Home 64-bit |
| Processor | Intel Core i3 (10th Gen) 10110U / 2.1 GHz (4.1 GHz) / 4 MB Cache |
| Memory | 8 GB DDR4 (1 x 8 GB) |
| Storage | 256 GB SSD |
| Optical Drive | No optical drive |

| | |
|-----------------------|--|
| Display | 14"LED backlight 1366 x 768 / HD |
| Graphics | Intel UHD Graphics |
| Input Device | ClickPad |
| Integrated Webcam | Yes |
| Networking | 802.11a/b/g/n/ac,Bluetooth 5.0,Gigabit Ethernet |
| Battery | 2-cell - up to 14 hours |
| Security | Firmware Trusted Platform Module (TPM) Security Chip |
| Colour | Dark blue,tile black (keyboard) |
| Dimensions (WxDxH) | 32.8 cm x 22.48 cm x 1.89 cm |
| Weight | 1.55 kg |
| Manufacturer Warranty | EMEA warranty - 1 year - carry-in |

Extended Specification

General

| | |
|------------------|--------------------------------|
| Product Type | Notebook |
| Operating System | Windows 10 Home 64-bit Edition |

Processor / Chipset

| | |
|-----------------|---|
| CPU | Intel Core i3 (10th Gen) 10110U / 2.1 GHz |
| Max Turbo Speed | 4.1 GHz |
| Number of Cores | Dual-Core |
| Cache | 4 MB |

Memory

| | |
|-------------------|-----------------|
| RAM | 8 GB (1 x 8 GB) |
| Max RAM Supported | 16 GB |
| Technology | DDR4 SDRAM |
| Speed | 2666 MHz |
| Rated Speed | 2666 MHz |
| Slots Qty | 1 |
| Empty Slots | 0 |

Storage

| | |
|--------------|---------------------|
| Main Storage | 256 GB SSD M.2 SATA |
|--------------|---------------------|

Display

| | |
|--------------------------|-----------------|
| Type | 14" |
| LCD Backlight Technology | LED backlight |
| Resolution | 1366 x 768 (HD) |
| Widescreen | Yes |
| Features | Anti-reflective |

Audio &Video

| | |
|--------------------|--------------------|
| Graphics Processor | Intel UHD Graphics |
|--------------------|--------------------|

| | |
|--------|----------|
| Camera | Yes - HD |
|--------|----------|

| | |
|-------|---------------------------------|
| Sound | Stereo speakers,two microphones |
|-------|---------------------------------|

Input

| | |
|------|-------------------|
| Type | Keyboard,ClickPad |
|------|-------------------|

Communications

| | |
|----------|--------------------------------|
| Wireless | 802.11a/b/g/n/ac,Bluetooth 5.0 |
|----------|--------------------------------|

| | |
|-------------------|------------------|
| Network Interface | Gigabit Ethernet |
|-------------------|------------------|

Battery

| | |
|------------|--------------------|
| Technology | 2-cell Lithium Ion |
|------------|--------------------|

| | |
|----------|----------------|
| Run Time | Up to 14 hours |
|----------|----------------|

AC Adapter

| | |
|-------|-------------------------|
| Input | AC 120/230 V (50/60 Hz) |
|-------|-------------------------|

| | |
|--------|------------|
| Output | 19 V,2.1 A |
|--------|------------|

Connections &Expansion

| | |
|------------|--|
| Interfaces | USB-C 3.1 Gen 1 (supports DisplayPort Alt Mode) (Power Delivery/data/video) 2 x USB 3.1 HDMI Headphone/microphone combo jack LAN |
|------------|--|

| | |
|--------------------|---------------|
| Memory Card Reader | Yes (microSD) |
|--------------------|---------------|

Software

| | |
|-------------------|-------------------------------|
| Software Included | Microsoft 365 (30 days trial) |
|-------------------|-------------------------------|

Miscellaneous

| | |
|--------|---------------------------------|
| Colour | Dark blue,tile black (keyboard) |
|--------|---------------------------------|

| | |
|----------|--|
| Security | Firmware Trusted Platform Module (TPM) Security Chip |
|----------|--|

| | |
|----------|----------------------|
| Features | Antimicrobial finish |
|----------|----------------------|

| | |
|----------------------------|---|
| Theft/Intrusion Protection | Security lock slot (cable lock sold separately) |
|----------------------------|---|

| | |
|--------------------|--------------------------|
| Security Slot Type | Kensington security slot |
|--------------------|--------------------------|

| | |
|----------------------|---------------|
| Included Accessories | Power adapter |
|----------------------|---------------|

| | |
|---------------------|-----------------|
| Compliant Standards | JIS Z 2801:2010 |
|---------------------|-----------------|

Dimensions &Weight

| | |
|--------------------|------------------------------|
| Dimensions (WxDxH) | 32.8 cm x 22.48 cm x 1.89 cm |
|--------------------|------------------------------|

| | |
|--------|---------|
| Weight | 1.55 kg |
|--------|---------|

Manufacturer Warranty

| | |
|------------------|-----------------------------------|
| Service &Support | EMEA warranty - 1 year - carry-in |
|------------------|-----------------------------------|

What's in the box

Dynabook Satellite Pro C40-G-111
Power adapter

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet