

Dynabook Satellite Pro C50-H-11G(A1PYS33E118H)  
Dynabook Satellite Pro C50-H-11G - Core i3 1005G1 / 1.2 GHz - Win 10 Home 64-bit - 8 GB RAM - 256 GB SSD - 15.6" 1920 x 1080 (Full HD) - UHD Graphics - Wi-Fi 5,Bluetooth - dark blue,black (keyboard)



No-compromise style,productivity and value. Meet your company's technology goals and your IT budget with a stylish device you'll be proud to use. The Satellite Pro C50 is equipped with a powerful processor,fast RAM,USB Type-C port for one-click connection to your favorite peripherals and features a special antibacterial paint coating that inhibits the growth of microorganisms such as bacteria.

Key Selling Points

- Non-glare FHD screen
- USB Type-C,HDMI,SD card reader,USB Type-A,Gigabit LAN and Wi-Fi
- HD webcam,Microsoft Cortana-enabled microphone and stereo speakers
- Trusted Platform Module (TPM) 2.0,fingerprint reader,user and administrator password access

Product Features

- Designed to look the part  
Entry-level price,executive looks. The sleek Satellite Pro C50 is thin and lightweight. Its non-glare FHD screen affords the device a compact footprint. Yet it remains a pleasure to use at the desk or on the road thanks to its ergonomic keyboard,full numeric keypad and long battery life. It also features ClickPad with integrated fingerprint reader in dynabook's portfolio,supporting Precision Touch Pad technology for accurate control,no mouse required.
- Makes any environment your workspace  
It may be compact,but the dynabook Satellite Pro C50 is fully loaded with connectivity. Its USB Type-C port supports charging,external display and data transfer. Meanwhile,an HDMI port provides easy sharing on external screens,and fast and reliable Gigabit LAN and Wi-Fi enable effortless network access. And if you need to quickly swap files or connect peripherals,its SD card reader,pair of USB Type-A ports and built-in Bluetooth have you covered.
- Be there without going there  
Seamless communication with customers and colleagues is super important. The Satellite Pro C50 is ready for action in this regard. It comes with everything you need to video conference,including an HD webcam,Microsoft Cortana-enabled microphone and stereo speakers.
- Security you can trust  
Peace of mind comes as standard with the Satellite Pro C50. Enterprise-ready security features such as firmware-based Trusted Platform Module (TPM) 2.0,a fingerprint reader,and user and administrator password access help keep valuable data out of the wrong hands,while the built-in Kensington lock slot ensures the laptop stays right where you left it.

Main Specifications

Product Description	Dynabook Satellite Pro C50-H-11G - 15.6"- Core i3 1005G1 - 8 GB RAM - 256 GB SSD
Product Type	Notebook
Operating System	Win 10 Home 64-bit
Processor	Intel Core i3 (10th Gen) 1005G1 / 1.2 GHz (3.4 GHz) / 4 MB Cache
Memory	8 GB DDR4 (1 x 8 GB)
Storage	256 GB SSD
Optical Drive	No optical drive
Display	15.6"LED backlight 1920 x 1080 / Full HD
Graphics	Intel UHD Graphics
Input Device	ClickPad
Numeric Keypad	Yes
Integrated Webcam	Yes

Networking	802.11a/b/g/n/ac,Bluetooth 4.2,Gigabit Ethernet
Battery	2-cell - up to 9.5 hours
Security	Firmware Trusted Platform Module (TPM) Security Chip
Colour	Dark blue,black (keyboard)
Dimensions (WxDxH)	36.25 cm x 24.05 cm x 1.97 cm
Weight	1.76 kg
Manufacturer Warranty	EMEA warranty - 1 year - carry-in

Extended Specification

General

Product Type	Notebook
Operating System	Windows 10 Home 64-bit Edition

Processor / Chipset

CPU	Intel Core i3 (10th Gen) 1005G1 / 1.2 GHz
Max Turbo Speed	3.4 GHz
Number of Cores	Dual-Core
Cache	4 MB

Memory

RAM	8 GB (1 x 8 GB)
Max RAM Supported	16 GB
Technology	DDR4 SDRAM
Speed	3200 MHz
Rated Speed	3200 MHz
Slots Qty	1
Empty Slots	0

Storage

Main Storage	256 GB SSD M.2 SATA
--------------	---------------------

Display

Type	15.6"
LCD Backlight Technology	LED backlight
Resolution	1920 x 1080 (Full HD)
Widescreen	Yes
Image Aspect Ratio	16:9
Features	HighBrightness,anti-reflective,Full HD eDP

Audio &Video

Graphics Processor	Intel UHD Graphics
Camera	Yes - HD
Camera Features	Privacy shutter
Sound	Stereo speakers,two microphones

Input

Type	Keyboard,ClickPad
Numeric Keypad	Yes

Communications

Wireless	802.11a/b/g/n/ac,Bluetooth 4.2
Wireless Controller	Intel Dual Band Wireless-AC 3165
Network Interface	Gigabit Ethernet

Battery

Technology	2-cell Lithium Ion
Run Time	Up to 9.5 hours

AC Adapter

Input	AC 120/230 V (50/60 Hz)
Output	19 V,2.1 A

Connections &Expansion

Interfaces	USB-C 3.1 Gen 1 (supports DisplayPort Alt Mode)
	2 x USB 3.0
	HDMI
	Headphone/microphone combo jack
Memory Card Reader	LAN
	Yes (microSD)

Software

Software Included	Microsoft 365 (30 days trial)
-------------------	-------------------------------

Miscellaneous

Colour	Dark blue,black (keyboard)
Security	Firmware Trusted Platform Module (TPM) Security Chip
Features	Antimicrobial finish
Theft/Intrusion Protection	Security lock slot (cable lock sold separately)
Security Slot Type	Kensington security slot
Included Accessories	Power adapter
Compliant Standards	JIS Z 2801:2010

Dimensions &Weight

Dimensions (WxDxH)	36.25 cm x 24.05 cm x 1.97 cm
Weight	1.76 kg

Manufacturer Warranty

Service &Support	EMEA warranty - 1 year - carry-in
------------------	-----------------------------------

What's in the box

Dynabook Satellite Pro C50-H-11G  
Power adapter

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet