
PUSH WIRE® connector for junction boxes; for solid and stranded conductors; max. 2.5 mm<sup>2</sup>; 4-conductor; transparent housing; orange cover; Surrounding air temperature: max 60°C; 2,50 mm<sup>2</sup>; multicoloured



www.wago.com/773-164





## Item description

#### Note:

### **Terminating Aluminum Conductors**

WAGO spring clamp terminal blocks are suitable for solid aluminum conductors up to 4 mm²/12 AWG if WAGO "Alu-Plus" Contact Paste is used for termination.

"Alu-Plus" Contact Paste Advantages:

- Automatically destroys the oxide film during clamping.
- Prevents fresh oxidation at the clamping point.
- Prevents electrolytic corrosion between aluminum and copper conductors (in the same terminal block).
- Provides long-term protection against corrosion.

For spring clamp connections with PUSH WIRE® connection technology, WAGO recommends that the aluminum conductor first be cleaned and then immediately inserted into the clamping unit filled with "Alu-Plus" contact paste.

It is also possible to apply WAGO "Alu-Plus" additionally on the whole surface of the aluminum conductor before termination.

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/773-164



Please note that the nominal currents must be adapted to the reduced conductivity of the aluminum conductors::

 $2.5 \text{ mm}^2 = 16 \text{ A}$ 

4 mm<sup>2</sup> = 22 A

Safety information 1:

in grounded power lines

#### Data

### **Electrical data**

# Ratings per IEC/EN

Ratings per	IEC/EN 60664-1
Nominal voltage (II/2)	400 V
Rated surge voltage (II/2)	4 kV
Rated current	24 A
Legend (ratings)	(II / 2) ≙ Overvoltage category II / Pollution degree 2

### Connection data

Connection technology	PUSH WIRE <sup>®</sup>
Actuation type	Push-in
	Push-in
Connectable conductor materials	Copper
	Aluminum
	Copper
	Aluminum
Solid conductor	0.75 2.5 mm² / 18 12 AWG
Stranded conductor	1.5 2.5 mm² / 16 12 AWG
Strip length	12 mm / 0.47 inch
Total number of connection points	4
Total number of potentials	1
Wiring direction	Side-entry wiring

# Physical data

Width	13 mm / 0.512 inch
Height	13.1 mm / 0.516 inch
Depth	19.5 mm / 0.768 inch

### Material data

Color multicoloured

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/773-164



Cartificata

Cover color	orange
Flammability class per UL94	V2
Fire load	0.057 MJ
Weight	2.7 g

# **Environmental requirements**

Surrounding air temperature (operation) 60 °C

### Commercial data

Product Group	7 (Push Wire Conn.)
Packaging type	box
Country of origin	DE
GTIN	4044918398022

# Approvals / Certificates

### **Country specific Approvals**

Logo	Approval	Additional Approval Text	name
	CSA	C22.2	15411
<b>GB</b>	DEKRA Certification B.V.		(LR46759)

### **UL-Approvals**

Logo Approval Additional Approval Text name

UL UL 486C E69654



**UL International Germany GmbH** 

## Optional accessories

#### General accessories

Item no.: 249-130
Syringe; Contents: 20 ml Alu-Plus contact paste

www.wago.com/249-130

# Mounting adapter

Item no.: 773-332

Mounting carrier; 773 Series - 2.5 mm² / 4 mm² / 6 mm²; for DIN-35 rail mounting/screw mounting; www.wago.com/773-332

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/773-164



**Downloads** 

Documentation

**Additional Information** 

Technical explanations Apr 3, 2019 pdf Download

2.2 MB

Download

CAD/CAE-Data

CAE data

WSCAD Universe 773-164 URL Download

EPLAN Data Portal 773-164 URL Download

**Environmental Product Compliance** 

Compliance Search

**Environmental Product Compliance 773-164** URL

PUSH WIRE® connector for junction boxes; for solid and stranded conductors; max. 2.5 mm<sup>2</sup>; 4-conductor; transparent housing; orange cover; Surrounding air

temperature: max 60°C; 2,50 mm2; multicoloured

**Installation Notes** 

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.