



## The D2 two-tape system

Separate ink and label tape cassettes allow you to mix and match image and tape colours to achieve 18 colour combinations and a variety of widths. Print up to three different colours on the same label. 6, 12, 19, 24 and 32 mm wide label tapes (10 m) and 6 colours.



### Removable

Label can be removed leaving a clean surface



### Surfaces

Sticks to almost all clean flat surfaces (plastic, paper, metal, wood, glass)



### Easy peel

For convenient removal of the liner



### Water resistant

Resistant to water and most weak solvents



### UV

Resists ultraviolet exposure

### Which tapes work with your DYMO labeller?

Types	6mm	9mm	12mm	19mm	24mm	32mm
LabelManager 9000	✓	✓	✓	✓	✓	✓
PC-10	✓	✓	✓	✓	✓	✓
DYMO 6000	✓	✓	✓	✓	–	–
DYMO 9000	✓	✓	✓	✓	✓	✓



## D2 labels

DYMO tape cassettes, self-adhesive and with back-slits<sup>1</sup> to ensure easy separation.

Colour	Length = 10m Width	Length = 10m				
		6mm <sup>1</sup>	12mm	19mm	24mm <sup>2</sup>	32mm <sup>2</sup>
transparent		S0721020	S0721080	S0721140	S0721200	S0721240
white		S0721030	S0721090	S0721150	S0721210	S0721250
yellow		S0721060	S0721120	S0721180	S0721230	S0721280
blue		S0721050	S0721110	S0721170	S0721220	S0721270
green		S0721070	S0721130	S0721190	–	S0721290
red		S0721040	S0721100	S0721160	–	S0721260
	Packaging quantity	1/5	1/5	1/5	1/5	1/5

## D2 ink ribbons

Ink ribbons to be used in conjunction with D2 tape cassettes.

Colour	Length = 50m Width	Length = 50m	
		9mm	19mm <sup>2</sup>
black		S0721300	S0721330
red		S0721310	S0721340
blue		S0721320	S0721350
	Packaging quantity	1/5	1/5

<sup>1</sup> 6 mm tape is without back-slit

<sup>2</sup> not for DYMO 6000