

PRODUCT-DETAILS

OBEA10

OBEA10 CONTACT BLOCK



General Information

Extended Product Type	OBEA10
Product ID	1SCA022190R3000
EAN	6417019108452
Catalog Description	OBEA10 CONTACT BLOCK
Long Description	Protection degree IP20.

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85389099
Country of Origin	Finland (FI)

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC390084M0003

Dimensions

Product Net Width	9 mm
Product Net Height	42 mm

Product Net Depth / Length	28 mm
Product Net Weight	0.008 kg

Technical

Conventional Free-air Thermal Current (I _{th})	10 A
Conventional Thermal Current (I _{the})	Fully Enclosed 10 A
Number of Auxiliary Contacts NO	1

Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	N/A

Certificates and Declarations (Document Number)

Environmental Information	N/A
Instructions and Manuals	1SCC390084M0003

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	10 mm
Package Level 1 Depth / Length	50 mm
Package Level 1 Height	40 mm
Package Level 1 Gross Weight	0.014 kg
Package Level 1 EAN	6417019108452

Classifications

Object Classification Code	N/A
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
UNSPSC	39121522
WEEE Category	Product Not in WEEE Scope
E-Number (Finland)	3641278
E-Number (Sweden)	3171501

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Change-over and Transfer Switches Accessories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches Accessories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Switch Fuses Accessories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Switch-Disconnectors Accessories

Low Voltage Products and Systems → Switches → Switch Disconnectors Accessories

