



## Laser Instruments - Line Lasers

### DW087K



#### DW087K Features

- Self-levelling cross line laser is accurate to  $\pm 0.3$  mm/m in levelling applications
- Self-Levelling up to 4 degrees surface angle with automatic out of level indication, marks a levelled line in seconds
- 2 button operation and low battery indication for ease of use
- Built in magnetic pivot bracket mounts easily on metal surfaces
- Overmolded housing helps maintain calibration under jobsite conditions
- Includes 3 x AA batteries for 20 plus hours runtime
- Kit box protects unit and helps maintain calibration when stored in gang box

#### DW087K Specifications

Laser class	2, <1mW
Accuracy	+/-0.3 mm/m
Number of beams	2
Direction of beams	vertical/level
Indoor visibility range	15 m
Self-Levelling Range	+/-4 °
Power Supply	4.5V - 3x AA
Tripod connection	1/4"
Weight	0.46 kg
Width	61 mm
Length	112 mm
Height	113 mm

#### DW087K Standard

- 3 x AA size alkaline batteries
- Wall mount bracket
- Heavy duty carrying case