



HDC | HDC HQ

TE Internal #: T2080122101-000

HDC HQ, Rectangular Contact Inserts, Pin, Contact Insert Pole Configuration 12, Crimp Terminal, 12 Position, 26 – 14AWG Wire Size

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Pin**

Contact Insert Pole Configuration: **12**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **12**

Sealable: **No**

Features

Product Type Features

Product Type	Contact Insert
Sealable	No

Configuration Features

Number of Positions	12
---------------------	----

Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	12
Contact Current Rating (Max)	10 A

Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

Dimensions

Wire Size	26 – 14 AWG
-----------	-------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2021 (211)</p> <p>Candidate List Declared Against: JAN 2021 (211)</p> <p>SVHC > Threshold:</p> <p>Pb (3.7% in Pb-Alloy in Copper)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1010031100-000
H3A-KDTP



TE Part # T3609200102-000
DLX-20-M



TE Part # T1329030120-000
H3A-MTG-M20



TE Part # T2020001025-000
CDM-2.5



TE Part # T2080122201-000
HQ-012-F

Also in the Series | **HDC HQ**



[Rectangular Contact Inserts\(15\)](#)

Customers Also Bought

TE Part #TAA751A1611-002
Fieldbus, DeviceNet M12 A-Code 5p
PVC

TE Part #T1240160140-000
H16B-TGH-M40

TE Part #T1319030120-000
H3A-MTS-M20

TE Part #T1329030120-000
H3A-MTG-M20

TE Part #T1230160140-000
H16B-TSH-M40

TE Part #T2010042201-000
HA-004-F

TE Part #T2020002008-000
CDF-0.75

TE Part #T2020002015-000
CDF-1.5

TE Part #T1330060125-000
H6B-TSH-M25

TE Part #T1410160000-000
H16B-AG-SL

Documents

Product Drawings

[HQ-012-M](#)

English

CAD Files

[3D PDF](#)

[3D](#)



Customer View Model

[ENG_CVM_CVM_T2080122101-000_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2080122101-000_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2080122101-000_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

Agency Approvals

[Agency Approval Document](#)

English