

Stock no 63516

### Bit Set In Full Plus Drawer EVA Insert Tray (167 Piece)

Expert Quality, selection of bits for automotive and workshop use, manufactured from S2 steel, which is correctly hardened and tempered, with a satin chromed finish. Supplied complete in a two tone full plus drawer EVA insert tray made from closed cell foam. Suitable to be used in Draper and Draper Expert tool chests and other manufacturers similar tool chests.

#### **Contents:**

- 1 x 3/8" Sq Dr x 10mm Hex adaptor
- 1 x 1/2" Sq Dr x 10mm Hex adaptor
- 5 x 1/4" E sockets: E4, E5, E6, E7, E8
- 4 x 3/8" E sockets: E10, E11, E12, E14
- 5 x 1/2" E sockets: E16, E18, E20, E22, E24
- 8 x 1/4" Draper TX - STAR<sup>®</sup> socket bits: T8, T9, T10, T15, T20, T25, T27, T30
- 5 x 3/8" Draper TX - STAR<sup>®</sup> socket bits: T40, T45, T47, T50, T55
- 2 x 1/2" Draper TX - STAR<sup>®</sup> socket bits: T60, T70
- 5 x 1/4" hex socket bits: H3, H4, H5, H6, H7, H8
- 4 x 3/8" hex socket bits: H9, H10, H12, H14mm
- 2 x 1/2" hex socket bits: H17, H19mm
- 8 x 1/4" plain slot socket bits: 3, 4, 4.5, 5, 5.5, 6, 6.5, 7mm
- 4 x 1/4" cross slot socket bits: No.0, No.1, No.2, No.3
- 4 x 1/4" PZ Type socket bits: No.0, No.1, No.2, No.3
- 13 x Long arm hex keys: 1.3, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 8, 10mm
- 9 x Long arm Draper TX - STAR<sup>®</sup> keys: T10, T15, T20, T25, T27, T30, T40, T45, T50
- 10 x 30mm Draper TX - STAR<sup>®</sup> bits: T20, T25, T30, T40, T45, T47, T50, T55, T60, T70
- 10 x 30mm Draper TX - STAR<sup>®</sup> security bits: T20T, T25T, T30T, T40T, T45T, T47T, T50T, T55T, T60T, T70T
- 8 x 30mm Hex bits: 4, 5, 6, 7, 8, 10, 12, 14mm
- 9 x 30mm Ribe bits: M5, M6, M7, M8, M9, M10, M12, M13, M14
- 6 x 30mm Spline bits: M5, M6, M8, M10, M12, M14
- 10 x 75mm Draper TX - STAR<sup>®</sup> bits: T20, T25, T30, T40, T45, T47, T50, T55, T60, T70
- 10 x 75mm Draper TX - STAR<sup>®</sup> security bits: T20T, T25T, T30T, T40T, T45T, T47T, T50T, T55T, T60T, T70T
- 8 x 75mm Hex bits: 4, 5, 6, 7, 8, 10, 12, 14mm
- 9 x 75mm Ribe bits: M5, M6, M7, M8, M9, M10, M12, M13, M14
- 6 x 75mm Spline bits: M5, M6, M8, M10, M12, M14

<b>Dimensions</b>	560 x 390 x 30mm
-------------------	------------------