



## Main

|                          |                                       |
|--------------------------|---------------------------------------|
| Range                    | Spacial                               |
| Product name             | Spacial SBX                           |
| Device application       | Multi-purpose                         |
| Category                 | Industrial box                        |
| Device short name        | SBX                                   |
| Enclosure type           | Flat face box                         |
| Enclosure nominal height | 300 mm                                |
| Enclosure nominal width  | 300 mm                                |
| Enclosure nominal depth  | 120 mm                                |
| Enclosure mounting       | Wall mounted                          |
| Device composition       | 4 cover screw<br>1 cover<br>1 body    |
| Body type                | Single piece body folded and welded   |
| Type of front cover      | Plain door                            |
| Cover fixing             | Half turn metal screw                 |
| Lock type                | Captive screw PZ2 outside sealed area |
| Removable parts          | Cover by captive screws               |

## Complementary

|                         |                              |
|-------------------------|------------------------------|
| Material                | Stainless steel 304L         |
| Surface finish          | Scotch-Brite® brushed        |
| Standards               | IEC 62208                    |
| Product certifications  | BV<br>BVM<br>UL              |
| IP degree of protection | IP66 conforming to IEC 60529 |

|                                     |                              |
|-------------------------------------|------------------------------|
| IK degree of protection             | IK10 conforming to IEC 62262 |
| Ambient air temperature for storage | -35...60 °C                  |
| Operating temperature               | -35...80 °C                  |
| Net weight                          | 3.6 kg                       |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 3.324 kg |
| Package 1 Height             | 31.5 cm  |
| Package 1 width              | 31.5 cm  |
| Package 1 Length             | 14 cm    |

## Offer Sustainability

|                            |                                                                                                                       |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                 |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                     |
| REACH free of SVHC         | Yes                                                                                                                   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                     |
| Mercury free               | Yes                                                                                                                   |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                         |