



Main

Range	Spacial
Product name	Spacial SBX
Device application	Multi-purpose
Category	Industrial box
Device short name	SBX
Enclosure type	Flat face box
Enclosure nominal height	200 mm
Enclosure nominal width	400 mm
Enclosure nominal depth	120 mm
Enclosure mounting	Wall mounted
Device composition	4 cover screw 1 cover 1 body
Body type	Single piece body folded and welded
Type of front cover	Plain door
Cover fixing	Half turn metal screw
Lock type	Captive screw PZ2 outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	Stainless steel 304L
Surface finish	Scotch-Brite® brushed
Standards	IEC 62208
Product certifications	BV BVM UL
IP degree of protection	IP66 conforming to IEC 60529

IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Operating temperature	-35...80 °C
Net weight	3.2 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.078 kg
Package 1 Height	41.5 cm
Package 1 width	21.5 cm
Package 1 Length	13.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile