

Energizer® Vision Lantern

ALU45

The *Energizer®* Vision Lantern is a bright and powerful lighting option for various tasks. Its high lumen output in combination with a long runtime and power bank capabilities provides a reliable 360 lighting for adventures, outdoor activities, emergency situations, and it can also be used to charge devices via a USB port out. The design provides a steady base for hands-free operation and the comfortable non-slip grip handle makes it easy to carry. With the *Energizer®* Vision Lantern, you can customize the light output as needed by using its dimming feature, or for a low diffused light use the night light mode. This lantern works on 4 D batteries.



Provides up to 1000 Lumens of Light*



Provides Run Time of up to 8h**



Sustains 1 Meter Drop Test



Water Resistant IPX4 – works after splashing water on all sides

DESIGN BENEFITS

- ✓ Durable construction
- ✓ Dimming Feature for customized light output and optimal runtime
- ✓ Powerful and Bright 360 area lighting
- ✓ Steady base for hands-free and comfortable non-slip grip makes it easy to carry.

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Operates on 4D Batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
Power consumption 8.25W / Battery D
Energizer E95 6.0V dc
LED Specifications: LED 3.0V cc / 2750 mA

CERTIFICATES AND COMPLIANCE

CE RoHS

EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

*Light output measured from LED. Value is only applicable to the LED. Actual device light output may vary.
**Endpoint determined at 1% of initial value using Energizer® MAX® batteries.

Results based on: Energizer MAX Alk / E95

PERFORMANCE BENEFITS

- ✓ Long runtime
- ✓ Up to 10X Brighter than standard LED technology
- ✓ High mode for maximum brightness
- ✓ Night Light
- ✓ USB Port out – charges devices
- ✓ Powerful light even after a full smartphone charge***

SPECIFICATIONS

Weight Excluding Batteries:

581 Grams / 1.3 lb

Dimensions:

158.6mm x 72mm x 254mm /
6.22" x 2.83 x 10"

NUMBER OF OPERATING MODES: 3

Mode	Lumens (lm)	Runtime (h)
High	1000*	8**
Low	100*	170**
Night Light	--	--

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.

This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty.

©2018 Energizer