GSM400 Air Quality CO_2 Meter

Handheld Meter Measures CO_2, Temperature, Humidity, Wet Bulb and Dew Point

Features:

- Simultaneously displays CO_2, Temperature and Relative Humidity
- TWA (Time Weighted Average - 8 hours)
- STEL (Short Term Exposure Limit - 15 minute weighted average)
- NDIR (non-dispersive infrared) waveguide technology
- Backlit triple LCD display
- Min/Max records the highest and lowest readings
- Data Hold freezes the reading on the display
- User-adjustable CO_2 alarm level
- °F/°C selectable
- Auto power off with disable
- Includes (4) AA batteries and carrying case

Applications:

Monitor air quality in office buildings, schools, exhibition halls, shopping malls, meeting rooms, fitness centers, restaurants and other public places.

Specifications

Carbon Dioxide (CO_2)	0 to 9999ppm
Accuracy	±(5% + 30ppm) (0 to 5000ppm)
Air Temperature	14 to 140°F (-10 to 60°C)
Accuracy	±0.9°F/0.6°C
Relative Humidity	0 to 99.9%RH
Accuracy	±3%RH (10 to 90%RH)
Wet Bulb	23 to 140°F (-5 to 60°C)
Dew Point	-4 to 140°F (-20 to 60°C)
CO2 Alarm	100 to 9900ppm in 100ppm steps
Power	4 AA batteries
Dimensions	7.9 x 2.7 x 2.3" (200 x 70 x 57mm)
Weight	6.7oz (190g)

Ordering Information:

GSM400 Air Quality CO_2 Meter

RoHS CE

TRIPLETT Test Equipment & Tools

850 Perimeter Road • Manchester, NH • (603) 669-6400 • info@triplett.com