




NYLON 6/6 (RMS-01) COLOR: NATURAL PART NO.	FLAME RET. (RMS-19) COLOR: NATURAL PART NO.	DIM. "A"
MSPM-2-01	MSPM-2-19	1/8 (3.2)
MSPM-3-01	MSPM-3-19	3/16 (4.8)
MSPM-4-01	MSPM-4-19	1/4 (6.4)
MSPM-5-01	MSPM-5-19	5/16 (7.9)
MSPM-6-01	MSPM-6-19	3/8 (9.5)
MSPM-7-01	MSPM-7-19	7/16 (11.1)
MSPM-8-01	MSPM-8-19	1/2 (12.7)
MSPM-9-01	MSPM-9-19	9/16 (14.3)
MSPM-10-01	MSPM-10-19	5/8 (15.9)
MSPM-12-01	MSPM-12-19	3/4 (19.1)
MSPM-13-01	MSPM-13-19	13/16 (20.6)
MSPM-14-01	MSPM-14-19	7/8 (22.2)
MSPM-16-01	MSPM-16-19	1 (25.4)
MSPM-18-01	MSPM-18-19	1-1/8 (28.6)
MSPM-20-01	MSPM-20-19	1-1/4 (31.8)
MSPM-22-01	MSPM-22-19	1-3/8 (34.9)
MSPM-24-01	MSPM-24-19	1-1/2 (38.1)

TITLE: MINI SUPPORT POST, MICRO			DWG IN IN (MM)		FINAL	
E	REMOVED NOTES; ADDED COLUMN "-19" AND CHANGED FILE NO.	SM 08.15.02	FILE # MSPM		DWN: P.B.	APP:
D	TOP VIEW ADDED	J.L. 12.8.98	MAT'L: SEE TABLE		DT: 03-11-94	DT:
C	MAT'L RMS-19 ADDED	J.L. 12.29.97	RE:		PART #	
B	ADDED -13 PART NO.	RT 11.06.96			MSPM-SERIES	
A	ADDED -9 PART NO.	JB 04.19.96			PRINT TYPE	
REV	DESCRIPTION	ENGR DATE			CA	