




Order Code	TCK-154
Inductance	4.7 μ H $\pm$ 20% (at 1 kHz / 1 V)
Impedance (DCR)	109 m Ω max.
Rated Current	1.15 A max.
Operating Temperature	-40°C to +125°C



Impedance Curve




Outline Dimensions



Dimensions [mm]

A	4.0 $\pm$ 0.5
B	4.5 $\pm$ 0.5
C	3.2 $\pm$ 0.5
D	1.2 typ.
E	4.5
F	1.75
G	1.5



PCB PATTERN

