



Quality Products. Service Excellence.

Knockdown Rack Cabinet *RCK Series*

1,050 lbs (476 kg) Weight Capacity



We designed our new RCK Cabinet series for your Homelab and Pro-AV applications. We've included loads of unique features such as bonus rack units, compatibility for standard hardware components, and more. Every RCK is self-squaring and takes just minutes to assemble. In addition, each cabinet has mounting points for our easy four-screw field-installable doors.

Features

- Available in six (6) heights and two (2) depths.
- Optional locking doors are constructed in 16-gauge steel. The doors install in minutes and are available in solid, vented, and tinted window.
- Doors include a locking swing handle **compatible with electronic locking handles**.
- The ready-to-assemble self-squaring cabinet body is constructed in 16-gauge steel and includes vents for **optional fans** on the cabinet sides.
- Includes two (2) pairs of adjustable depth 10-32 threaded EIA compliant rack rails.
- Both the top and bottom-rear of cabinet feature a removable conduit knockout 1U panel. The top-rear can be used as a bonus 1U rack mounting point for equipment or rack accessory.
- The front of the cabinet includes at both top and bottom a steel plate. When removed reveals a Decora® compatible mounting point.
- Numerous cable tie-off points included for front-to-rear cable management.
- Cabinet top includes solid top panel and conduit knockouts for additional cable entry.
- Cabinet base also includes mounting holes for optional **casters** or **leveling feet**.
- Both top and cabinet base include an opening compatible with interchangeable "1923" sized **top panels**.
- Cabinet ganging kit included.
- Includes 50-pack of **SCREW1032-50** screws.



Specifications

- Cabinet frame constructed in 16-gauge steel.
- Mounting rails constructed in 12-gauge steel.
- Top-Rear of cabinet included 3.00", 2.50" and 2.0" knockouts for conduit.
- Rear 1U panels include 1.375", 1.125" and 0.675" knockouts.
- Include multiple bonding and grounding points.
- Load rated for up to 1,050 lbs (476 kg). Rolling caster load rated for up to 600 lbs (272 kg)
- Finished in sand-textured black powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Leveling Feet
- Cabinet Top Panels
- Rack Shelves
- Bonding Wire Kits
- Door Lock Replacement Kit
- Locking Door
- Rack Mount Basic PDU
- Rack Panels
- Protective Grommet Strip

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
Black							
RCK12U25BK	26.38	24.00	25.00	12U + 1U	21.00	19.00	22.56
RCK18U25BK	36.50	24.00	25.00	18U + 1U	31.50	19.00	22.56
RCK20U25BK	40.00	24.00	25.00	20U + 1U	35.00	19.00	22.56
RCK24U25BK	47.00	24.00	25.00	24U + 1U	42.00	19.00	22.56
RCK36U25BK	68.00	24.00	25.00	36U + 1U	63.00	19.00	22.56
RCK42U25BK	78.50	24.00	25.00	42U + 1U	73.50	19.00	22.56
RCK12U32BK	26.38	24.00	32.00	12U + 1U	21.00	19.00	29.56
RCK18U32BK	36.50	24.00	32.00	18U + 1U	31.50	19.00	29.56
RCK20U32BK	40.00	24.00	32.00	20U + 1U	35.00	19.00	29.56
RCK24U32BK	47.00	24.00	32.00	24U + 1U	42.00	19.00	29.56
RCK36U32BK	68.00	24.00	32.00	36U + 1U	63.00	19.00	29.56
RCK42U32BK	78.50	24.00	32.00	42U + 1U	73.50	19.00	29.56

The +1U refers to the 1U usable accessory mounting at the top-rear of the cabinet.

Optional Doors

Use with Cabinet Height	Part No. Solid	Part No. Vented	Part No. Window
12U	RCKSD12UBK1	RCKVD12UBK1	RCKWD12UBK1
18U	RCKSD18UBK1	RCKVD18UBK1	RCKWD18UBK1
20U	RCKSD20UBK1	RCKVD20UBK1	RCKWD20UBK1
24U	RCKSD24UBK1	RCKVD24UBK1	RCKWD24UBK1
36U	RCKSD36UBK1	RCKVD36UBK1	RCKWD36UBK1
42U	RCKSD42UBK1	RCKVD42UBK1	RCKWD42UBK1

Optional Mounting Rails

Part No.	Part No.	Usable Mounting Dimensions		Overall Cabinet
Threaded 10-32	Square Hole	Rack Units	Height	Width
H1TRR12U24BK	H1SRR12U24BK	12U	21.00	24.00

Part No. Threaded 10-32	Part No. Square Hole	Usable Mounting Dimensions		Overall Cabinet Width
		Rack Units	Height	
H1TRR18U24BK	H1SRR18U24BK	18U	31.50	24.00
H1TRR20U24BK	H1SRR20U24BK	20U	35.00	24.00
H1TRR24U24BK	H1SRR24U24BK	24U	42.00	24.00
H1TRR36U24BK	H1SRR36U24BK	36U	63.00	24.00
H1TRR42U24BK	H1SRR42U24BK	42U	73.50	24.00

Optional Casters

Part No.	Strength	Style/ Material	Wheel Diameter	Overall Height		Hole Mounting Pattern		Caster Set Weight Capacity	Qty Included In Set	Qty with Brakes Included
				Added to Cabinet		Width	Depth			
1425BLSOFT	Light Duty	Soft Thermoplastic	2.95	3.50		1.75	3.00	660 lbs (299 kg)	4	4
1425BM	Medium Duty	Hard Composition	3.00	3.81		1.75	3.00	700 lbs (318 kg)	4	0
1425BH	Heavy Duty	Hard Composition	3.00	3.81		1.75	3.00	1,050 lbs (476 kg)	4	0
1425BHLOCK	Heavy Duty	Hard Composition	3.00	3.81		1.75	3.00	1,050 lbs (476 kg)	4	4

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	RCK Top	
1	RCK Bottom	
2	RCK Side Panel	
2	Pair of Adjustable Rails	H1R Series
1	Solid Top/Bottom Panel with Hardware	C2T1923SBK1
2	1U Knockout Panel with Hardware	
8	Door Hinge Cover Plate with Hardware	
2	Decora Cover Plate with Hardware	
16	Rail Mounting Hardware (Spring-Nut and Bolt)	1421SN
16	M6 Cabinet Assembly Hardware	
2	Ganging Brackets	
50	10-32 x 0.75in Rack Mounting Screws	SCREW1032-50
1	Assembly Instructions	BUL88117

Data subject to change without notice