

AMPLIMITE

TE Internal #: 205556-2

Box Mount D-Sub Connectors, Plug, Cable-to-Cable, 9 Position, 1

D-Sub Shell Size, Pin, 20 D-Sub Contact Size, 2.77mm [.109in]

Centerline, Wire & Cable

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors

Connector & Housing Type: **Plug**Connector System: **Cable-to-Cable**Number of Positions: **9**Power/Signal/Coax Combination: **No**D-Sub Shell Size: **1****Features****Product Type Features**

Product Type	Connector
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Blindmate	No

Configuration Features

Number of Positions	9
Power/Signal/Coax Combination	No

Body Features

Retention Clip Material	Stainless Steel
Shell Plating Material	Cadmium
Shell Material	Steel
Non-Magnetic	No

Contact Features

Contact Type	Pin
Contact Mating Area Plating Material	Gold



Contact Base Material	Copper Alloy
D-Sub Contact Size	20
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Signal

Industry Standards

NASA Qualification	No
--------------------	----

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Size 20 contacts supplied with connectors are loose piece.
---------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.2% in component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 601966-5
K13-1 POSITIONER



TE Part # 601966-1
CRIMPING TOOL M22520/2-01

Customers Also Bought



TE Part #1-1879444-6
TE 100W 18R 5% Bracket



TE Part #204519-2
AMPLIMITE,ASY,PLUG,STD,90,4



TE Part #205161-1
AMPLIMITE,ASY,RCPT,STD,109,1



TE Part #205089-1
HD 20 PIN CONTACT



TE Part #205090-1
HD 20 SOCKET CONTACT




TE Part #109858-000
D-181-1222-90/9



TE Part #1-2221860-2
AMPLIMITE IP67,SZ2, 90, 26 POS,IFS, PLUG



TE Part #1-1532177-9
M83513/04-G03C, MCKS-C2-B-51S6G9-18.0



Documents

Product Drawings

[AMPLIMITE,ASY,PLUG,STD,109,1](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_205556-2_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205556-2_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205556-2_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940_Sec8_amplimite](#)

English

Product Environmental Compliance

[MD_205556-2_110620112315](#)

English

[MD_205556-2_110620112315](#)

English

Agency Approvals

[UL Report](#)

English