



### Main

Range	Spacial
Product name	Spacial SBX
Device application	Multi-purpose
Category	Industrial box
Device short name	SBX
Enclosure type	Flat face box
Enclosure nominal height	200 mm
Enclosure nominal width	200 mm
Enclosure nominal depth	80 mm
Enclosure mounting	Wall mounted
Device composition	4 cover screw 1 cover 1 body
Body type	Single piece body folded and welded
Type of front cover	Plain door
Cover fixing	Half turn metal screw
Lock type	Captive screw PZ2 outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	Stainless steel 304L
Surface finish	Scotch-Brite® brushed
Standards	IEC 62208
Product certifications	BV BVM UL
IP degree of protection	IP66 conforming to IEC 60529

IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Operating temperature	-35...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.62 kg
Package 1 Height	21.5 cm
Package 1 width	21.5 cm
Package 1 Length	10 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>



### Main

Anwendung	Multi-purpose
Range	Spacial
Product or component type	Rail
Accessory / separate part category	Mounting accessory
Type of rail	Symmetrical DIN
Enclosure nominal dimensions	-
Mounting support	Self-tapping screw
Range compatibility	Spacial SBM
Device composition	1 rail
Quantity per set	Set of 10

### Complementary

Material	Steel
Surface finish	Zinc coated
Fixing mode	By screw - screw type Ø5 mm self-tapping screws - rear of enclosure location
Height	35 mm
Width	185 mm nominal: 164 mm fixing centers:
Depth	7.5 mm
Thickness	1 mm
Net weight	0.062 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	62 g

Package 1 Height	18.5 cm
Package 1 width	4.5 cm
Package 1 Length	4 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>