



26 Group Lock Box

Part Number: 152189

Overview

The 26 Group Lock Box provides the ultimate in simplicity, storage and security for large group-lockout scenarios.

- Up to 26 workers can lock on per box
- Easy to wall-mount with button mount holes
- Clear viewing panel gives you a clear view of equipment
- Center-hanging ops lock identifies the lockout coordinator or shift manager
- Locking tabs fully secure viewing panel and prevent key removal, regardless of lock point in use
- 11 hooks store up to three 1.5 in.- or 3 in.-shackle padlocks and keys

Specifications

Key Characteristics	Product Number	152189
	UPC	888434559284
	UOM	Each
	Brand Name	Brady®
	Country of Origin	China
	HTS Code (Harmonized Tariff Schedule)	3926.90.9985
	ECCN (Export Commodity Control Number)	EAR99
	Dimensions	11 in H x 13 in W x 4 in D
Dimensions	Height	11 in
	Width	13 in
	Depth	4 in
Material Characteristics	Material	Plastic
	Lockout Box Material	Plastic
	Color	Red
	Service Temperature Range °F	-40 °F - 248 °F
	Minimum Service Temperature °F	-40 °F
	Maximum Service Temperature °F	248 °F
Product Features	Application	Lockout Tagout
	Cabinet Mounting Type	Wall Mounted
	Lockout Box Type	Wall Mount - Empty
	Maximum Number of Padlocks	27
	Maximum Number of Padlocks Stored	12
	Number of Hooks	11
	Wall-Mountable?	Yes
Compatibility	Maximum Shackle Diameter	0.47 in
Preprinted Information	Text Legend	GROUP LOCK/TAGOUT
Compliance	UNSPSC	46171509
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863