



M18 FUEL™ 3/8 Compact Impact Wrench w/ Friction Ring Kit

Part: 2854-22

INCLUDES

1 x M18 FUEL™ 3/8" Compact Impact Wrench w/ Friction Ring (2854-20)

2 x M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack (48-11-1850)

1 x M18™ & M12™ Multi-Voltage Charger (48-59-1812)

1 x Carrying Case

Our M18 FUEL™ 3/8" Compact Impact Wrench w/ Friction Ring Kit is the most compact in its class, delivering you the most access in tight spaces, up to 250 ft-lbs of nut-busting torque, and maximum workspace visibility. This battery-powered impact wrench measures only 4.8" in length with a POWERSTATE™ Brushless motor to provide the power to remove stubborn fasteners, even in confined spaces. The MILWAUKEE® 3/8" Compact Impact Wrench has tri-LEDs that surround the anvil to deliver you brighter light with fewer shadows. 4-Mode DRIVE CONTROL™ offers greater precision with a range

of pre-set RPM and IPM levels, selectable from a single button on the tool. By selecting Mode 4, AUTO SHUT-OFF™ control applies no more than 20 ft-lbs of torque for hand-tight fastening applications to prevent overtightening. Mode 4 also features Bolt Removal Control delivers full torque output, then decreases RPMs once the bolt is loosened to prevent fastener drops. REDLINK PLUS™ Intelligence electronics make these controls possible while ensuring maximum performance, protecting the tool against overloads, over-heating, and over-discharge. The included M18™ REDLITHIUM™ 5.0Ah battery pack fits M18™ tools, delivering more work per charge and more work over the life of the pack.

Key Features:

- Friction ring (hog ring) ensures quick and easy socket changes
- The POWERSTATE™ Brushless motor delivers up to 250 ft-lbs. of nut-busting torque
- 4-Mode DRIVE CONTROL™ provides greater control over output speed and power. Includes auto shut-off and bolt-removal mode
- Bolt Removal control delivers full torque output, then decreases RPMs once the bolt is loosened to prevent fastener drops
- Mode 1 IPMs: 0-1,000; Mode 2 IPMs: 0-2,400; Mode 3 IPMs: 0-3,500; Mode 4 IPMs: 0-3,500
- Works in up to to 69kV environments
- 4.8" in length provides most access in tight spaces
- Tri-LEDs deliver high definition lighting to increase workspace visibility with less shadows
- AUTO SHUT-OFF™ control prevents over tightening and increases productivity by applying no more than 20 ft-lbs. of torque
- Mode 1 RPMs: 0-800; Mode 2 RPMs: 0-1,650; Mode 3 RPMs: 0-2,400; Mode 4 RPMs: 0-2,400
- REDLINK PLUS™ Intelligence ensures maximum performance and protects from overloads, heating and over-discharge
- Compatible with all M18™ batteries & Chargers

BATTERY SPECIFICATIONS

Voltage: 18V

PRODUCT SPECIFICATIONS

Height: 7.95"

Length: 4.8"

Weight: 2.4 lbs

Width: 2.56"

Power Source: Cordless

Nut Busting Torque: 250 (ft-lbs)

Fastening Torque: 250 (ft-lbs)

Anvil Type: 3/8" Square w/ Friction Ring

Battery System: M18