

Smart Wireless Video Doorbell with Chime



SKU Code: SHA5307

Smart Wireless Video Doorbell with Chime



Features

1. See, Hear and speak to your visitors from your smartphone, from wherever you are.
2. Recommended for homes with or without existing doorbell wiring. Simply remove your existing doorbell and replace it with our PRO-Series Wireless Video Door Bell.
3. You'll get a notification when movement is detected or when visitors press the Doorbell.
4. Powered by the rechargeable battery pack. Comes with an easy to recharge battery (2x18650) which can last up to 6 months.
5. Monitors your home in 1080P HD video with infrared night vision. Lets you check-in on your property at anytime with Live View, real-time video.
6. Includes Plug in Chime which can be paired easily with our PRO-series Doorbell via RF433Mhz.

Video Doorbell Specifications

Resolution	: 1024*720 / 1920*1080
Recording Angle	: 166° Degree
IR ED	: 6*850mm
Wi-Fi	: IEEE 802.11 b/g/n
Audio	: Two-way talk, noise cancellation
Memory Type	: Micro SD Card (upto 64GB. Not included)
Battery	: 2 x 18650 Battery
Monitoring	: Doorbell button, motion detection, remote wake up
Power Consumption	: Standby: 20uA; Working: 170mA

*2 x 18650 battery (total 5200mAh) normally can supports 3-6 months usage.

Chime Specifications

Operating voltage	: AC 90V ~ AC 250V 50Hz/60Hz
Output power	: 0.15W
Standby power consumption	: ≤0.5mW
Operating current/static standby	: 120mA / 10mA
Optional music	: 60 songs optional
Volume	: 5 level adjustable (maximum volume up to 100 dB), minimum volume is silent
Working frequency	: 433.92 MHz±75KHz
Receive sensitivity	: -110dbm
Colour	: White
Size	: 70*45*48mm (UK PLUG)
Net weight	: 65G/PC
Product size	: 70*52*33mm