# NiMH Battery Charger (CHVC4E/CHVC4)

# **Basic Charger / Base Charger**

<u>Download Instructions (Americas)</u> <u>Download Instructions (Rest of World)</u>

### **ECONOMICAL**

 Most affordable *Energizer*<sub>®</sub> charger



### **EASY TO USE**

• Lights indicate batteries are charging



### **CONVENIENT**

• Charges 2 or 4 NiMH batteries





#### Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with *Energizer*® NiMH batteries.

#### **Product Detail:**

**Designation:** Basic Charger / Base Charger

Model: CHVC4E / CHVC4

Color: Black

**Charge Capability:** "AA" (2) or (4) / "AAA" (2) or (4)

"AA" (2) and "AAA" (2) Simultaneously

Note: When charging only 2 batteries, place batteries

in the two positions to the left or right.

Charging Times: Battery Capacity Estimated (estimated) (NiMH) (mAh) (time) 1300-2000 8-11 hrs AA AA 2000-2300 11-13 hrs AAA 500-800 7-10 hrs

Shutoff Mechanism: (CHVC4E) Timer Control: 15 hours

(CHVC4) None

Charging Current: "AA" 170-200mA

"AAA" 80-100mA

Trickle Charge: None

Input Rating (CHVC4E): 110V-127VAC, 50-60Hz, 6W Input Rating (CHVC4): 220V-240VAC, 50-60Hz, 6W

Typical Weight: 88 grams

**Dimensions (mm):** 105 x 70 x 70 (H x L x W) **Safety Features:** Reverse Polarity Protection

## **Important Notice**

This datasheet contains information specific to products manufactured at the time of its publication.

Contents herein do not constitute a warranty.