

- A. Barrel type banana plug with machined contour spring support. Crimped uniformly from 4 sides for maximum strength. Fits industry standard banana jack ≥ 4mm.
- B. Thermoplastic elastomer strain relief moulded on. Flex life average >1,000,000 cycles (ANSI/ESD S1.1). Break load average 13.5kg.
- C. Relaxed retraction coiled cord produces less tug force on wearer's wrist. Break load average 13.5kg. Wire insulation black colour PVC.
- D. Single T-2940 tinsel conductor. Consisting of 7 strands of polyester wrapped with copper. High flex life. Equivalent is 29 gauge (cir mil and/or ohms).
- E. Autosplice brass crimp secures conductors to resistor lead and provides stress relief for resistor.
- F. One megohm ±5%, 1/4 watt, series resistor limits current for operator safety.

- G. Spring loaded 4mm medical snap socket. Spring separation 3.18mm 4.19mm. Provides 0.45kg - 2.27kg breakaway from 4mm snap stud (ANSI/ESD S1.1). Compatible with most major brands.
- H. Charleswater logo moulded in compliance with ANSI/ESD S1.1.
- I. Date coded with date of manufacture.
- J. Underwriters Laboratory Listing 90P1C when used with Desco Europe wristbands.

Meets wrist strap cord requirements of IEC 61340-5-1 tested per IEC 61340-4-6. To be used with a <u>single-wire wristband</u> (not included).

			Socket Size	
Termination	Length	Resistor	4mm	10mm
Banana	1.8m	1 x 1 megohm	60341	
10mm Socket	1.8m	2 x 1 megohm	60334	<u>60318</u>





United States of America

Unless otherwise noted, tolerance ±10% Specifications and procedures subject to change without notice.

## **DESCO**EUROPE

## **Relaxed Retraction Coiled Cord**

DESCO EUROPE 2A DUNHAMS LANE, LETCHWORTH GARDEN CITY, HERTFORDSHIRE, SG6 1BE, UK PHONE: +44 (0) 1462 672005

E-MAIL: Service@DescoEurope.com, INTERNET: DescoEurope.com

Drawing Number 60318.E

**DATE:** February 2018