PSI Displays Ltd



Suite C2, Butts Business Centre, Butts Road, Chiseldon, Swindon, Wiltshire, SN4 0PP. UK.

Tel: +44 (0) 1793 740456

e-mail: sales@psidisplays.co.uk Website www.psidisplays.co.uk

LCD COLOUR MONITOR Model No. L101AP

10.1" TFT LCD Colour Video Monitor with LED Back Light, Stylish Slim Line Cabinet. HDMI, PC, Composite Video with BNC connector, Audio In and Out via speaker. I/R Remote control. Full OSD. 12volts. Low current operation. Auto start when Power connected to remembered input. Full screen mode converts 4:3 to Full screen image. Optional Sun Visor.



Main Features:

- Resolution: 1280 x 800 WXGA
- Picture Ratio: 16:10, 4:3 and Full Screen.
- Brightness: 350 cd/m2 LED Back Light.
- Contrast Ratio: 800:1
- Inputs: HDMI, PC, Composite BNC, Audio.
- Outputs: Audio via speaker.
- Mounting: Bottom & Rear "C" Mount, Stand for Desk or Wall mounting.
- Cabinet finished in Black.
- Speaker: 1 x 2 Watts max.

The L101AP is a Stylish Wide Screen Monitor with TFT technology, offers Professional sharp images and with high contrast ratio 800:1 and Brightness 350 cd/m2 gives superb pictures. With HDMI, PC and Composite video with BNC Connector, Audio In and Out via speakers making it a truly versatile Monitor. Mounting options offer a Stand for Desk and Wall mounting with Bottom and Rear "C" mount. Infra-Red remote control. All mounted in a Smart Slim line tough housing. This compact unit is ideal for Multimedia Video, Surveillance and General purpose systems applications.

SPECIFICATIONS:

- Active area: 216.96 x 135.6 (WxH)mm. 16.2M Colours. PAL and NTSC Auto.
- Response Time: 10/15ms (Tr/Tf). Viewing angle: Left/Right: 85°, Up/ Down 85°.
- Controls/Indicators: I/R sensor, On LED, Power, Up, Down, Select, Menu, Source.
- Power Source: 12V DC, 0.67 Amp, 7 Watts approx. AC Adaptor: 100-240V 50/60Hz 1Amp.
- Dimensions: 253 x 178 x 34.7. Carton: 335 x 285 x 109 (WxHxD)mm.
- Weight: Unit: 0.53 Kgms, Carton: 1.2 Kgms. Temp: Operation: 0~40°C.

Connections: HDMI Input: HDMI Socket, PC: 15 pin Sub-D socket. Composite Video In: BNC. Audio L & R In: 3.5mm stereo jack socket. (Audio Lead: 3.5mm Stereo Jack plug to BNC x 2 sockets). USB: For Service use only. DC input: 2.1mm socket.

Standard accessories: AC adapter, I/R Remote Control, Audio Lead. Desk/Wall stand.

Optional: Sun Visor or VESA 75mm Plate.

All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO