

PSI Displays Ltd



Suite C2, Butts Business Centre, Butts Road, Chiseldon, Swindon, Wiltshire, SN4 0PP. UK.

Tel: +44 (0) 1793 740456


e-mail: sales@psidisplays.co.uk Website www.psidisplays.co.uk

LCD COLOUR MONITOR Model No. L104AKL

10.4" TFT LCD Colour Video Monitor with LED Back Light, 1204 x 768, VGA, 2 x Composite Video In/Out BNC. Y/C (S-Video), Audio In/Out and via speakers. I/R Remote control. Optional: Glass Front, Touch screen, 19" Rack mounting. Other sizes available.



19" Rack Mount option.



Main Features:

- Resolution: 1024 x 768 - XGA
- Picture Ratio: 4:3
- Brightness: 350 cd/m2 LED Back Light.
- Contrast Ratio: 900:1
- Inputs: VGA, 2 x Composite video, S-Video
- Outputs: 2 x Composite Video, Audio.
- Picture in Picture (VGA/Video).
- Mounting: VESA 75 or 100, Key Hole, Stand.
- Slim Aluminium Cabinet finished in Black.
- Speaker: 2 Watts max.

The L104AKL with TFT technology, offers Professional sharp images and with high contrast ratio 900:1 and Brightness 350 cd/m2 gives superb pictures. With BNC Connectors, Video Loop through, Audio In/Out connectors and Audio via speakers making it a truly versatile Monitor. Mounting options offering VESA 75 + 100 & Key hole mounting and with a Desk stand. Infra-Red remote control. All mounted in a Smart tough Aluminium Metal housing. This compact unit is ideal for Multimedia Video and Surveillance systems applications.

SPECIFICATIONS:

- Active area: 211.2 x 158.4 (WxH)mm. • 16.7M Colours. • PAL and NTSC Auto.
- Response Time: 8/8ms (Tr/Tf). • Viewing angle: Left/Right: 75°, Up/ Down 75°.
- Controls/Indicators: Source, Menu, Item, Up, Down, Power. Front: On LED and I/R sensor.
- Power Source: 12V DC, 0.67 Amp, 8 Watts approx. AC Adaptor: 100-240V 50/60Hz 1.5Amps.
- Dimensions: 266 x 214 x 41 (51 with stand). Carton: 335 x 290 x 110 (WxHxD)mm.
- Weight: Unit: 2.3 Kgms, Carton: 3.10 Kgms. • Temp: Operation: 0~40°C, Storage: -20~ 60° C.

Connections: VGA: 15 pin Sub-D socket. Composite Video In/Out 1 & 2: BNC. Y/C (S- Video) In: 4 pin mini din socket, Audio Out 3.5mm Jack socket, Audio In/Out 1 & 2: Phono sockets. DC input: 2.1mm jack socket. AC adaptor: IEC socket.

Standard accessories: AC adapter, AC Mains Lead, I/R Remote Control.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO