

Hand Lawn Mower

GC-HM 300

Item No.: 3414114

Ident No.: 21010

Bar Code: 4006825651942

The Einhell GC-HM 300 cylinder lawn mower is a robust, functional lawn mower without a motor drive, for the clean, quiet and environment-friendly mowing of lawns of up to 150 m² in size. The ball-bearing mounted mower spindle with five high-grade steel blades is designed for a cutting width of 30 cm. The cutting height adjustment facility with 4 levels can be adjusted to individual requirements between 13 mm and 37 mm. The plastic roller has a diameter of 45 mm. The cylinder lawn mower has lawn-friendly large wheels. A curved long handle provides optimum on-the-job ergonomics. There is a parking position for easy and secure storage of the lawn mower. The 16 liter grass catch basket is removable and easy to empty.

Features & Benefits

- Mowing spindle with ball bearings and 5 high-grade steel blades
- 4-steps adjustable cutting height 13-37 mm
- Detachable 16 I grass basket
- Bended handle providing perfect ergonomics
- Parking position assuring safe and easy storage
- Plastic roller Ø 45 mm
- Wide wheels exert less stress on the lawn
- Recommended for lawn areas up to 150 m²

Technical Data

- Cutting width 300 mm - Cutting height adjustment - Mowing spindle diameter - Number of mowing knives - Capacity of catch bag - Wheels diameter
- 4 settings | 13-37 125 mm 5 Pieces 16 L 215 mm

Logistic Data

- Product weight
- Gross weight single packaging
- Dimensions single packaging
- Pieces per export carton
- Gross weight export carton
- Dimensions export carton
- Container quantity (20"/40"/40"HC)

6.5 kg 7.4 kg 478 x 355 x 245 mm 1 Pieces 7.4 kg 480 x 240 x 345 mm 700 | 1540 | 1700







