

SMALL CHAINS AND FITTINGS

CHAINS

Small Chains and Decorative Chains are used in a wide variety of industrial, commercial and domestic applications. Our range includes all the most popular chains – welded and unwelded – made either from solid brass or steel.


A choice of electroplated finishes such as chrome, nickel, zinc and bronze gives the most suitable protective and decorative appearance for each chain.

SMALL CHAINS



Curb Chain

∅ 1.2 - 2.2mm



Ball Chain

∅ 2.4 - 4.5mm



Chandelier Chain

13 - 24mm link length



Plumbers Chain

17 - 24mm link length



Oval Chain Welded

∅ 1.6 - 3.0mm



Single Link Jack Chain

∅ 1.6 - 4.0mm



Double Link Jack Chain

∅ 1.6 - 4.0mm



Knotted Chain

∅ 1.6 - 5.0mm

DECORATIVE CHAINS



Clock Chain

∅ 1.1 - 1.6mm



Twisted Chain

∅ 1.6mm



Double Oval Chain

∅ 1.6 - 1.8mm



Mattress Chain

∅ 1.6mm



Open-Joint Oval Chain

∅ 2.8 - 3.8mm



Gothic Chain

∅ 2.2 - 3.8mm



Standard Electro Chain

∅ 2.5 - 3.8mm



Square Chain

∅ 2.0 - 4.0mm

FITTINGS

Specially designed fittings are usually needed for fixing, joining or lengthening sections of chain or for making chain assemblies to standard specifications. We can supply these components as separate items or make complete assemblies to your design. For more detailed information on our specialist assembly service, please see our "Assemblies" section.

Ball Chain End Fittings	Ball Chain Connectors	Split (Key) Rings	Rings	Dee Rings	Ess Hooks	Consumer Hooks	Spring Hooks	Jump Rings Triangles

Ball Chains

Brass		
Product Code	Size	Ball Ø (mm)
101 24	No.3	2.4
101 32	No.6	3.2
101 40	No.8	4.0
101 45	No.10	4.5

Finishes: polished; chrome; nickel plated
Supplied: 10m boxes & reels; bulk on reels



Steel		
Product Code	Size	Ball Ø (mm)
103 24	No.3	2.4
103 32	No.6	3.2
103 45	No.10	4.5

Finish: nickel plated
Supplied: 10m boxes & reels; bulk on reels



Stainless Steel		
Product Code	Size	Ball Ø (mm)
107 24	No.3	2.4
107 32	No.6	3.2
107 45	No.10	4.5

Finish: polished
Supplied: 10m boxes & reels; bulk on reels

Key Chains

Steel		
Product Code	Length	
	(mm)	(ins)
063 62	100	4
063 64	150	6

Finishes: nickel plated
Supplied: 100 per box; bulk in 1000s



I/D Chains

Brass & Steel			
Product Code	Product Code	Length	
		(mm)	(ins)
061 42	063 42	690	27
061 44	063 44	760	30
061 46	063 46	915	36

Finishes: brass - chrome
 steel - nickel plated
Supplied: 100 per box; bulk in 1000s



Ball Chain Fittings

CONNECTORS

Brass	
Product Code	Size
121 03	No.3
121 66	No.6
121 88	No.8
121 99	No.10

Finishes: polished; nickel plated
Supplied: 100 per box; bulk in 1000s



Steel & Stainless Steel		
Product Code	Product Code	Size
123 03	127 03	No.3
123 66	127 66	No.6
123 99	127 99	No.10

Finishes: steel - nickel plated,
 stainless - polished
Supplied: 100 per box; bulk in 1000s



END ATTACHMENTS

Brass	
Product Code	Size
111 03	No.3
111 66	No.6
111 88	No.8
111 99	No.10

Finishes: polished; nickel plated
Supplied: 100 per box; bulk in 1000s



CUP ATTACHMENTS

Brass & Stainless Steel		
Product Code	Product Code	Size
131 66	135 66	No.6
131 99	-	No.8/10

Finishes: brass - polished; nickel plated
 stainless - polished
Supplied: 100 per box; bulk in 1000s



SLEEVES

Brass	
Product Code	Size
131 03	No.3
131 06	No.6

Finishes: polished; nickel plated
Supplied: 100 per box; bulk in 1000s



Oval Link Chain - Brass

Brazen		
Product Code	Link Length x Material (mm)	Imperial
331 08	8 x 1.4	5/16" x 17g
331 10	10 x 1.6	3/8" x 16g
331 13	13 x 1.8	1/2" x 15g
331 16	16 x 2.3	5/8" x 13g
331 19	19 x 2.5	3/4" x 12g
331 25	25 x 3.0	1" x 11g

Finishes: polished; chrome
Supplied: 10m hanks; 10m boxes & reels



Chandelier Chain

Brass		
Product Code	Size	Link Length x Material (mm)
151 13	109	13 x 0.35
151 16	127	16 x 0.45
151 19	128	19 x 0.50
151 22	136	22 x 0.75
151 25	165	25 x 0.95

Finishes: polished; chrome
Supplied: 10m hanks; 10m boxes & reels



Oval Link Chain - Steel

Welded		
Product Code	Link Length x Material (mm)	Imperial
333 13	13 x 1.8	1/2" x 15g
333 16	16 x 2.3	5/8" x 13g
333 19	19 x 2.5	3/4" x 12g
333 25	25 x 3.0	1" x 11g

Finishes: polished; zinc; black
Supplied: 10m hanks



Plumbers Chain

Brass		
Product Code	Size	Link Length x Material (mm)
151 94	194	17 x 0.70
151 96	196	24 x 1.20

Finishes: polished; chrome
Supplied: 10m hanks; 10m boxes & reels



Oval Link Chain - Stainless Steel

Welded		
Product Code	Link Length x Material (mm)	Imperial
335 12	13 x 1.6	1/2" x 16g
335 15	16 x 2.0	5/8" x 14g
335 18	19 x 2.3	3/4" x 13g
335 25	25 x 3.0	1" x 11g

Finish: polished
Supplied: 10m hanks



Clock Chain

Brass	
Product Code	Link Length x Material (mm)
161 13	13 x 1.6

Finishes: polished; chrome
Supplied: 10m hanks

Stainless Steel	
Product Code	Link Length x Material (mm)
165 19	19 x 2.0

Finish: polished
Supplied: 10m hanks



Trace Chain

Gilding Metal, Soldered

Product Code	Size	Material x Links/inch
162 37	22/15	0.022 x 15
162 39	28/12	0.028 x 12
162 41	32/9	0.032 x 9
162 43	40/8	0.040 x 8
162 45	45/6	0.045 x 6

Finish: *polished*
Supplied: *25m hanks*



Curb Chain

Steel - Unwelded

Product Code	Size	Material x Links/inch
163 25	35/10	0.035 x 10
163 27	48/8	0.048 x 8
163 29	55/5	0.055 x 5
163 31	75/5	0.075 x 5
163 33	90/3	0.090 x 3

Finish: *nickel*
Supplied: *25m hanks*



Jack Chain

Steel - Single Link

Product Code	Wire Ø (mm)	Link Length (mm)
303 16	1.6	20
303 20	2.0	22
303 25	2.5	25
303 30	3.0	33
303 40	4.0	40

Finishes: *polished; black; zinc*
Supplied: *10m hanks; 10m boxes*



Knotted Chain

Steel

Product Code	Wire Ø (mm)	Link Length (mm)
323 16	1.6	27
323 18	1.8	28
323 20	2.0	32
323 25	2.5	39
323 30	3.0	48
323 40	4.0	57
323 50	5.0	70

Finishes: *polished; zinc*
Supplied: *10m or 30m hanks; 10m boxes*



Brass - Single Link

Product Code	Wire Ø (mm)	Link Length (mm)
301 16	1.6	19
301 20	2.0	21
301 25	2.5	25

Finish: *polished*
Supplied: *10m hanks; 10m boxes*

Steel - Double Link

Product Code	Wire Ø (mm)	Link Length (mm)
303 50	1.6	17
303 53	2.0	19
303 55	2.5	25
303 57	3.0	30

Finishes: *polished; black; zinc*
Supplied: *10m hanks; 10m boxes*



Twisted Chain

Steel

Product Code	Wire Ø (mm)	Link Length (mm)
183 62	1.6	25

Finish: *zinc*
Supplied: *10m hanks*



Mattress Chain

Steel		
Product Code	Wire Ø (mm)	Link Length (mm)
183 52	1.6	24

Finish: zinc
Supplied: 10m hanks



Gothic Chain

Steel		
Product Code	Wire Ø (mm)	Inside Link (mm)
183 12	2.2	24 x 10
183 14	2.7	40 x 14
183 16	3.8	43 x 20

Finishes: e/brassed & lacquered
e/bronzed & lacquered
Supplied: 10m hanks



Double Oval

Steel		
Product Code	Wire Ø (mm)	Link Length (mm)
183 42	1.6	25

Finish: zinc
Supplied: 10m hanks



Square Chains

Steel		
Product Code	Wire Ø (mm)	Inside Link (mm)
183 22	2.0	17 x 5
183 24	3.0	29 x 9
183 26	4.0	29 x 9

Finishes: e/brassed & lacquered
e/bronzed & lacquered
Supplied: 10m hanks



Open Joint Oval

Steel		
Product Code	Wire Ø (mm)	Inside Link (mm)
183 02	2.8	24 x 10
183 04	3.2	40 x 14
183 06	3.8	43 x 20

Finishes: e/brassed & lacquered
e/bronzed & lacquered
Supplied: 10m hanks



Solid Brass Link - Welded

Brass - Welded		
Product Code	Wire Ø (mm)	Inside Link (mm)
451 42	5.0	21 x 9

Finish: polished
Supplied: per metre



Standard Electro

Steel		
Product Code	Wire Ø (mm)	Inside Link (mm)
183 32	2.5	29 x 10
183 34	2.8	35 x 10
183 36	3.8	39 x 12

Finishes: e/brassed & lacquered
e/bronzed & lacquered
Supplied: 10m hanks



Small Chains & Accessories

Consumer Hooks - Brass & Steel

Product Code	Product Code	Length x Material
Brass	Steel	(mm)
261 19	263 19	19 x 2
261 22	263 22	22 x 2
261 25	263 25	25 x 2.5
261 32	263 32	32 x 3
261 38	263 38	38 x 3
261 50	263 50	50 x 4



Finishes: brass - polished; nickel; chrome
steel - polished; zinc
Supplied: 100 per box; bulk in 1000s

Split (Key) Rings - Steel

Product Code	Outer Ø (mm)	Thickness (mm)
403 13	13.0	1.7
403 16	16.0	2.3
403 20	20.0	2.6
403 22	22.0	2.9
403 25	25.0	3.2
403 30	30.0	3.7
403 38	38.0	3.7
403 51	51.0	4.3



Finish: nickel
Supplied: 100 per box; bulk in 1000s

Ess Hooks - Brass & Steel

Product Code	Product Code	Length x Material
Brass	Steel	(mm)
271 19	273 19	19 x 2
271 22	273 22	22 x 2
271 25	273 25	25 x 2.5
271 32	273 32	32 x 3
271 38	273 38	38 x 3
271 50	273 50	50 x 4



Finishes: brass - polished; nickel; chrome
steel - polished; zinc
Supplied: 100 per box; bulk in 1000s

Rings - Steel

Product Code	Product Code	Inside Ø x Material
Unwelded	Welded	(mm)
413 13	423 13	13 x 2.5
413 16	423 16	16 x 2.5
413 19	423 19	19 x 3.0
413 25	423 25	25 x 3.0
413 26	423 26	25 x 4.0
413 30	423 30	30 x 4.0



Finishes: polished; nickel; zinc
Supplied: bulk in 1000s

Spring Hooks - Steel

Product Code	Length	
	(mm)	(ins)
283 28	28	1 1/8
283 38	38	1 1/2
283 45	45	1 3/4
283 50	50	2
283 60	60	2 3/8



Finish: nickel
Supplied: 100 per box; bulk in 1000s

Dee Rings - Steel

Product Code	Product Code	Inside Ø x Material
Unwelded	Welded	(mm)
373 13	383 13	13 x 2.0
373 16	383 16	16 x 2.5
373 19	383 19	19 x 2.8
373 25	383 25	25 x 3.0
373 30	383 30	30 x 4.0



Finishes: polished; nickel
Supplied: bulk in 1000s

Small Chains & Accessories



◆ PLUMBING CHAINS & ACCESSORIES

Plumbing Assembly Chains - Brass

Size (mm)	Description
3.2	No.6 Ball
13 x 1.6	Open-Joint Clock
13 x 1.8	Brazed Oval

Finish: *chrome*



◆ BATH, BASIN & SINK CHAINS

No. 6 Ball Chain Assemblies

Product Code	Length (mm)	Description
011 33	305	38mm Stay
011 53	380	38mm Stay
011 73	460	38mm Stay
011 35	305	Hook each end
011 55	380	Hook each end
011 75	460	Hook each end
011 37	305	Wood screw stay
011 57	380	Wood screw stay
011 77	460	Wood screw stay



Finish: *chrome*
Supplied: *100 per box; bulk in 1000s*

Chain Stays - Brass heads

Product Code	Size (mm)	Description
051 50	38	Chain stay, 7/32" Steel thread & nut
051 70	19	Woodscrewstay, Steel thread

Finishes: *heads - chrome*
threads & nuts - zinc
Supplied: *100 per box; bulk in 1000s*



Open - Joint Clock Chain Assemblies

Product Code	Length (mm)	Description
021 33	305	38mm Stay
021 53	380	38mm Stay
021 73	460	38mm Stay
021 35	305	Hook each end
021 55	380	Hook each end
021 75	460	Hook each end
021 37	305	Wood screw stay
021 57	380	Wood screw stay
021 77	460	Wood screw stay



Finish: *chrome*
Supplied: *100 per box; bulk in 1000s*

Fittings - Brass

Product Code	Size (mm)	Description
261 22	22 x 2	Con Hooks
441 25	11 x 2	Jump Rings
441 15	1.8	Triangles
441 14	2.0	Triangles

Finishes: *nickel; chrome*
Supplied: *100 per box; bulk in 1000s*



Brazed Oval Chain Assemblies

Product Code	Length (mm)	Description
031 33	305	38mm Stay
031 53	380	38mm Stay
031 73	460	38mm Stay
031 35	305	Hook each end
031 55	380	Hook each end
031 75	460	Hook each end
031 37	305	Wood screw stay
031 57	380	Wood screw stay
031 77	460	Wood screw stay



Finish: *chrome*
Supplied: *100 per box; bulk in 1000s*

Plugs with Triangles

Product Code	Size (mm)	Description
524 43	38	Black polythene
524 45	44	Black polythene

Supplied: *100 per box; bulk in 1000s*

