

# KERN HDA 100-1

Professional Shore hardness tester



## Construction

Casing material:	Plastic
Dimensions (WxDxH):	162 x 65 x 38 mm
Dimensions housing (WxDxH):	162 x 65 x 38 mm
Overall dimensions mounted (WxDxH):	162 x 65 x 38 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Precision (of [Max]):	1 %
Readability:	0,100
Weighing units:	Shore A

## Functions

Data hold function:	yes
Obtaining average:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

## Power supply

Battery:	2x1.5 V AAA
----------	-------------

## Category

Brand:	Sauter
Category:	Hardness testers

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 200 x 50 mm
Gross weight:	820 g
Net weight:	173 g
Shipping method:	Parcel service