

KERN HK-D

Premium durometer for hardness testing of metals



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	368 x 220 x 87 mm
Gross weight:	1,540 kg
Net weight:	450 g
Shipping method:	Parcel service

Construction

Casing material:	Cast aluminium alloys
Dimensions (WxDxH):	132 x 82 x 31 mm
Dimensions housing (WxDxH):	132 x 82 x 31 mm
Overall dimensions mounted (WxDxH):	132 x 82 x 31 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring capacity [Max]:	960
Measuring range (Min):	170
Precision (of [Max]):	1 %
Readability:	1
Sensor:	D
Weighing units:	HV HL HRC HRB HB

Display

Display digit height (large):	1,100 cm
-------------------------------	----------

Functions

All measurement directions possible (360°):	yes
Automatic recognition of the impact sensor:	yes
Obtaining average:	yes

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Battery:	2x1.5 V AA
Operating time:	200 h

Services (optional)

Factory calibration certificate:	961-131
----------------------------------	---------

Category

Brand:	Sauter
Category:	Hardness testers
Product Group:	Electronic Leeb hardness tester