

# KERN HO1K

Premium UCI hardness testing device for Rockwell, Brinell and Vickers



## Construction

|                                     |                  |
|-------------------------------------|------------------|
| Casing material:                    | Metal lacquered  |
| Dimensions (WxDxH):                 | 28 x 83 x 160 mm |
| Dimensions housing (WxDxH):         | 28 x 83 x 160 mm |
| Overall dimensions mounted (WxDxH): | 28 x 83 x 160 mm |

## Piktogramme

### STANDARD



### OPTION



## Measuring system

|                 |                      |
|-----------------|----------------------|
| Weighing units: | HV MPa HL HRC HRB HB |
|-----------------|----------------------|

## Functions

|   |     |
|---|-----|
| All measurement directions possible (360°): | yes |
| Function to set limits:                     | yes |
| Obtaining average:                          | yes |
| Statistical function:                       | yes |
| Visual ready signal:                        | yes |

## Power supply

|                                 |             |
|---------------------------------|-------------|
| Charging time:                  | 8 h         |
| Input voltage:                  | 110 - 240 V |
| Mains adapter/adaptor included: | EURO        |
| Operating time (Backlight off): | 12 h        |
| Operating time (Backlight on):  | 6 h         |

## Services (optional)

|                                  |         |
|----------------------------------|---------|
| Factory calibration certificate: | 961-270 |
|----------------------------------|---------|

## Category

|           |                  |
|-----------|------------------|
| Brand:    | Sauter           |
| Category: | Hardness testers |

## Packaging & shipping

|                               |                    |
|-------------------------------|--------------------|
| Delivery:                     | 24 h               |
| Dimensions packaging (WxDxH): | 395 x 315 x 140 mm |
| Gross weight:                 | 5 kg               |
| Net weight:                   | 500 g              |
| Shipping method:              | Parcel service     |
| UN number:                    | 3481               |