

CHERRY KC 1000



Models may vary from the image shown

Perfect price/performance for office users

CHERRY KC 1000 is rock-solid CHERRY technology with an excellent price/performance ratio. Modern, flat design with gentle, quiet and durable abrasion-resistant keys. Universal, reliable and optimized for professional use. In black or gray.

Key benefits

- Flat, corded keyboard including cursor and number pad
- Whisper keystroke keys with durable key inscription
- Up to 10 million keystrokes
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Plug & Play via USB connection
- 3 blue status LEDs
- Optimised for professional use in the office (GS approval)
- Awarded the "Blaue Engel" environmental seal

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

530 g

Total weight (with packaging):

725 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 50°C

Current Consumption:

max. 50 mA

Interface:

- USB

Product approvals:

Product dependant, see table "Models"

System requirements:

- USB connection

Delivery Volume:

- CHERRY KC 1000
- Operating instructions in hard copy

Dimensions (product):

458 x 170 x 20 mm

Packaging dimensions:

480 x 205 x 27 mm

Reliability:

- MTBF (90) > 80,000 hours

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 4

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 32

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and

other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Product approvals	Number of Keys
1	CHERRY KC 1000	JK-0800BE-0	4025112082115	Belgium	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
2	CHERRY KC 1000	JK-0800BE-2	4025112082122	Belgium	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
3	CHERRY KC 1000	JK-0800BU-2	4025112097102	Bulgaria	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
4	CHERRY KC 1000	JK-0800CH-0	4025112082238	Switzerland	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
5	CHERRY KC 1000	JK-0800CH-2	4025112082689	Switzerland	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
6	CHERRY KC 1000	JK-0800DE-0	4025112081309	Germany	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
7	CHERRY KC 1000	JK-0800DE-2	4025112081316	Germany	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
8	CHERRY KC 1000	JK-0800ES-0	4025112082191	Spain	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
9	CHERRY KC 1000	JK-0800ES-2	4025112081347	Spain	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Product approvals	Number of Keys
10	CHERRY KC 1000	JK-0800EU-0	4025112081484	US English with EURO symbol	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, KCC, TÜV-Süd/GS	104+4
11	CHERRY KC 1000	JK-0800EU-2	4025112081491	US English with EURO symbol	black	black	c-tick, UL, CE, FCC, BSMI, KCC, TÜV-Süd/GS	104+4
12	CHERRY KC 1000	JK-0800FR-0	4025112082207	France	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
13	CHERRY KC 1000	JK-0800FR-2	4025112081323	France	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
14	CHERRY KC 1000	JK-0800GB-0	4025112082184	UK	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
15	CHERRY KC 1000	JK-0800GB-2	4025112081330	UK	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
16	CHERRY KC 1000	JK-0800IT-0	4025112082221	Italy	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
17	CHERRY KC 1000	JK-0800IT-2	4025112082702	Italy	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4
18	CHERRY KC 1000	JK-0800KR-2	4025112082054	English (US) / Korean	black	black	c-tick, UL, CE, FCC, BSMI, KCC, TÜV-Süd/GS	104+4
19	CHERRY KC 1000	JK-0800PN-0	4025112082214	Pan-Nordic	pale grey	pale grey	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Product approvals	Number of Keys
20	CHERRY KC 1000	JK-0800PN-2	4025112082696	Pan-Nordic	black	black	c-tick, UL, CE, FCC, BSMI, TÜV-Süd/GS	105+4