

PRODUCT-DETAILS

2522

1/2 CORD CONNECTOR .375-.500 RANGE



General Information

Extended Product Type	2522
Product ID	7TBD105230R0002
EAN	5414363101604
Catalog Description	1/2 CORD CONNECTOR .375-.500 RANGE
Long Description	Liquidtight Strain Relief Cord Connector, 1/2 Inch, Straight, Cord Range 0.375 to 0.500 Inch, Die Cast Zinc

Additional Information

Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Product Type	Strain Relief Cord Connectors-Straight

Ordering

EAN	5414363101604
UPC	786210025223
Customs Tariff Number	7907002000

Technical

Number of Batteries	0
Color	Metallic

Material	Zinc Die Cast
Size	1/2 Inch

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	25 piece
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 1 Width	4.5 in 114 mm
Package Level 2 Units	100 piece
Package Level 2 Height	4.2 in 107 mm
Package Level 2 Depth / Length	11.1 in 282 mm
Package Level 2 Width	9.8 in 249 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000046
Instructions and Manuals	2522

Classifications

UNSPSC	39121431
--------	----------

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

