

# Printers KERN 911-013



# Matrix needle printer KERN 911-013

For printing weighing results on normal paper, which is ideal for long-term archiving

# **Technical data**

- · Needle print
- · Speed: 1,8 line/s
- Max. 40 characters per line
- Width of the paper strip: 57 mm wide
- Operation via mains adapter 230 V/50 Hz (standard EU), as standard
- · Dimensions housing: W×D×H 100×180×106 mm
- · Not suitable for KERN PNS/PNJ, PES/PEJ
- · Interface cable not included with delivery

Price printer without interface cable, KERN 911-013

### Accessories

- · Paper rolls (10 pcs.), KERN 911-013-010
- · Universal mains adapter, standard EU/GB/US, KERN ABS-A01





#### Important note for printer orders:

Please state your balance model when ordering, so that the printer can be preconfigured in the factory to suit your balance.

#### Individual header data:

For printers KERN 911-013, YKN-01, YKB-01N and YKE-01 (in combination with YKI-02) the free software KERN SHM-01 can be used to print 4 header lines on the printout (see marking on balance). Compatible models: KERN 440, DE, FCB, FKB-A, PCB, PCD.