

# KERN TVO500N300

Premium test stand for laboratory applications



## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	600 x 500 x 280 mm
Gross weight:	38 kg
Net weight:	25 kg
Shipping method:	Freight forwarder

## Construction

Casing material:	Metal lacquered
Dimensions (WxDxH):	570 x 428 x 236 mm
Dimensions housing (WxDxH):	570 x 428 x 236 mm
Direction of measurement:	vertical
Maximum generated force:	500 N
Maximum travelling distance:	27 cm
Operation speed:	300 mm/min
Operation speed:	15 mm/min
Overall dimensions mounted (WxDxH):	570 x 428 x 236 mm
Speed accuracy (of [Max]):	2 %

## Piktogramme

### STANDARD



### OPTION



## Display

Display digit height (large):	1,400 cm
Display digit height (small):	9 mm

## Functions

Electrical limit swichtes:	yes
Repeat function:	yes

## Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	230 V AC 50 Hz
Mains adapter/adapter included:	EURO

## Category

Brand:	Sauter
Category:	Test stands
Product Group:	Electronic test stand