

Printers KERN YKN-01

**Matrix needle printer KERN YKN-01**

For printing weighing results on normal paper, which is ideal for long-term archiving

Technical data


- Needle print
- Speed: 1 line/s
- Max. 16 characters per line
- Width of the paper strip: 44 mm wide
- Operation via mains adapter 230 V/50 Hz (standard EU/GB/USA), as standard
- Dimensions housing:
W×D×H 158×106×40 mm
- Interface cable not included with delivery

Accessories

- Paper rolls (10 pcs.), KERN 911-013-010
- Universal mains adapter, standard EU/GB/US, KERN ABS-A01

Price printer without interface cable,
KERN YKN-01

STANDARD

**Important note for printer orders:**

Please state your balance model when ordering, so that the printer can be preconfigured in the factory to suit your balance.

Individual header data:

For printers **KERN 911-013, YKN-01, YKB-01N and YKE-01 (in combination with YKI-02)** the free software **KERN SHM-01** can be used to print 4 header lines on the printout (see marking on balance). Compatible models: KERN 440, DE, FCB, FKB-A, PCB, PCD.