

# OMEGAETTE™ Mini Current Clamp Meter

HHM221



- Pocket Size**
- DATA HOLD Function**
- Autoranging**
- Battery Life Approx. 300**
- 3½ Digital Liquid Crystal LCD, Maximum Reading 1999**
- Sampling 2 times/sec**
- Two 1.5 V, “AAA” Batteries (Included)**

## Specifications

**Numerical Display:** 3½ digital liquid crystal (LCD), maximum reading 1999

**Battery Life:** 300 hours approximately

**Low Battery Indication:** The low battery indicator light is displayed as needed

**Sampling:** 2 times/sec

**Power Source:** Two 1.5 V, “AAA” batteries (included)

**Operation Temperature and Humidity:** 0 to 40°C (32 to 104°F) below 80% RH

**Storage Temperature and Humidity:** -10 to 60°C (14 to 140°F) below 70% RH

**Rating:** IEC 1010; 300 V CAT III; 600 V CAT II

**Jaw Opening Diameter:** Cables 25 mm (1")

**Dimensions:** 29 H x 50 W x 187 mm L (1.14 x 1.97 x 7.36")

**Weight:** Approximately 210 g (0.46 lb)

## Electrical Specifications

ACA Function (Autorange)		
Range	Resolution	Accuracy
200 A	0.1 A	±2% rdg + 5 digits
400 A	1 A	

ACV Function (Autorange)		
Range	Resolution	Accuracy
200 V	0.1 V	±1.5% rdg + 5 digits
600 V	1 V	

Ohm Function		
Range	Resolution	Accuracy
200 Ω	0.1 Ω	±1.9% rdg + 3 digits

Continuity	
Range	Active Sound Level
)))	≤100 Ω



HHM221.

## To Order

Model No.	Description
HHM221	Mini current clamp meter
HHM-NIST	NIST-traceable calibration certificate

*Comes complete with carrying case, 2 “AAA” batteries, test leads, and operator’s manual.*

**Ordering Example:** HHM221, mini current clamp meter.