

IP-BASED KVM SWITCHING & EXTENSION

Agility™ is a scalable system for sending KVM, audio, and serial signals to user stations or video monitors as far as your Ethernet network goes. The flexible topology of the Agility gives you signal extension options beyond traditional keyboard-monitor-mouse. Get KVM switching, server sharing, video extension with full HD60fps, and multicasting. It's ideal when you need to share real-time video in various settings, such as in public safety, healthcare, education, and corporate applications.

Save valuable rackspace by adding the world's smallest Zero U KVM Transmitter to your Agility system. The dongle-sized device extends up to HD video (DVI or DisplayPort) and USB and can be powered over USB, consuming less than 3W.



PIXEL PERFECT

No-loss compression minimises bandwidth while maximising the user experience. Agility™ delivers perfect digital video: single link up to 1080p, dual link up to 2560 x 1600.

FLEXIBLE NETWORKING

Configure your network to suit your needs: point-to-point extension, KVM switching, single-target sharing or multicasting.

RESILIENCE

Link and power redundancy options. Auto-failover of system controllers.

SCALABLE

Add transmitters and receivers as your network grows; Agility scales to >2,000 endpoints.

MULTICASTING

Multicast DVI, USB, audio channels selectively, either single or as a group.

MANAGED MATRIX SWITCHING

iPath controller option offers enterprise user management, including authentication and access privileges or to tie in with third-party cross-point controlling via API.

