


**RoHS
Compliant**



120mm AC Axial Fan, Wire-Form Finger Guard, 72" Power Cord.


MC36455 - AC Axial Fan



Specifications

Dimension	: 120mm × 120mm × 38mm
Rated Voltage	: 115V AC 50 / 60 Hz
Operating Voltage	: 100 to 125V AC
Air flow	: 80 CFM
Noise level	: 34 dBA
UL	: E175395

MC32651 - Finger Guard




Specifications

Material	: C1008 steel.
Plating	: Bright nickel chrome.
Ring Diameter	: 2.3 mm.
Rib Diameter	: 2.3 mm

Dimensions : Inches (Millimetres)

MC32797 - 45° Plug, Power Cord



Specifications

Wire	: SPT1 105°C, 300 volts, black
Plug	: NEMA 1-15P
Length	: 72 inches (1829mm)
UL	: E348035, E345335

Part Number Table

Description	Part Number
Fan Kit	MC36428
Wire Guard	MC32651
120mm AC Axial Fan	MC36455
45° Plug, Power Cord, 72"	MC32797

Dimensions : Inches (Millimetres)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro