



ADS35DF 100V LINE MIXER AMPLIFIER

Features:

- Compact mini size public address amplifier
- Rated power 35W, 70V/100V & 4-8-16Ω output
- Line 1-2 input of RCA input and one RCA line output
- Mic 1 of 6.35mm in front panel with priority & muting
- Mic 2 of balanced XLR in rear panel
- Fire alarm: A closed contact will mute all other inputs except Mic 1
- Priority level: MIC1 - Fire Mute - others
- Power supply: AC 110-240V & DC 24V

TECHNICAL SPECIFICATIONS

Model:	ADS 35DF	Temperature :	-20degC / 50degC
Rated Power Output:	70V/100V support 4-16ohm	Phantom Power:	Yes (Mic 2)
Power Output (RMS):	35W	Tone:	Bass +/-10dB (100Hz), Treble +/-10dB (10kHz)
AC Power:	10-240V/50-60Hz.	Dimensions:	H50 x W250 x D225
AC Power Consumption:	52W	Weight:	Gross 3.10kg
Frequency Response:	Mic => 100Hz - 10kHz / Line => 80Hz - 16k Hz		
THD:	=/< 0.2% (1kHz, 1/3 output voltage)		
Line Input:	775mV		
Mic Inputs:	5mV		
Other Mic Inputs:	Mic 2 XLR (Rear Panel)		
with	gain control		
Priority Mic Input:	Mic 1 6.3mm Jack (Front Panel) wit		
Line Outputs:	1V RMS		
Loudspeaker Outputs:	Com 4-16ohm, 70V/100V		