



# CHERRY MC 9620 FPS - Customisable high-end mouse with innovative extras and progressive design

Detailed work requires a steady hand. Whether you're editing videos and graphics, or if you want to select lines of code and text precisely. With our wired CHERRY MC 9620 FPS computer mouse you're covered. With a resolution of up to 12,000 dpi, you always have complete control over the cursor, even on high-resolution displays. An illuminated DPI button shows the set resolution. The speed can be regulated up to 250 IPS (inch per second) for a guaranteed smooth experience.

Its great sensitivity means the wired mouse is also excellent for gaming after work. The integrated LED RGB lighting can be adjusted in a spectrum of 16.8 million colours using the downloadable CHERRY gaming software. Analog and digital signal processing progressively regulate functions in a similar way to a gaming controller.

The mouse can be ergonomically adapted using three insertable weights and a palm rest that can be extended in five positions. The Teflon sliding surfaces on the underside ensure stable guidance on almost all surfaces. The high-quality materials and progressive design allow the mouse to fit perfectly in your hand.

The CHERRY MC 9620 FPS mouse connects directly to your PC or laptop via USB and is ready for use immediately thanks to Plug & Play.



# **Function and performance**

- → Flexible, customisable gaming mouse with 9 buttons
- → CHERRY button for CHERRY Utility software to individualise the mouse settings
- → Simple weight adjustment with the 3 x 5 g weights included.
- → Ergonomic and fits every hand size thanks to a 5 stage extendable palm rest.
- → Extra-large Teflon glide pads for smooth and stable mouse movements
- → Complete colour spectrum can be illuminated in 16.8 million colours (RGB) with many different illumination effects and logo projection.
- → 5 freely programmable profile settings for dpi resolution can be set in the software. Can be changed with the dpi switches, displayed via white status lights.
- → Extremely durable thanks to high-quality materials including a braided cable and textured side grip surfaces

## **Technical data**

#### **Housing colour:**

black

## Weight (Product):

Ca. 145 g (including weights)
Ca. 130 g (without weights)

## Total weight (with packing):

Ca. 240 g

## Cable length:

Ca. 200 cm

#### Storage temperature:

-20 °C to 60 °C

# **Operating temperature:**

0 °C to 50 °C

## **Current consumption:**

max. 250 mA

#### **Connection:**

USB

## **Product approvals:**

- CE
- FCC
- KCC
- cROHS

## **System requirements:**

**USB-connection** 

#### Operating system:

Windows 7,10

## Scope of delivery:

CHERRY MC 9620 FPS

3 x 5 g weights

Operating manual

#### **Dimensions:**

Mouse: ca. 128 x 68,5 x 39,5 mm Packing: ca. 171 x 149 x 59 mm

Reliability:

Lifetime scrolling wheel: over 100.000 cycles

Lifetime mouse buttons: over 20 million mouse clicks

## Mouse:

Sensor: Pixart PMW-3360

Scanning: optical

Resolution: up to 12.000 dpi (adjustable)

Switches: Omron Number of buttons: 9

Mouse wheel design: scroll wheel with button function

Design: symmetric

# Packing unit:

Number of products in box: 10

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

# CHERRY MC 9620 FPS



#### Warranty:

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the

additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase. CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the

customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item..

# Models

	Product-Name	Product-number	EAN-Code
1	CHERRY MC 9620 FPS	JM-9620	4025112089831