


PART NO.

R-134G7210300CB

		REVISIONS						
ECN#	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	А	RELEASED	Veena	21/04/09	Suresh	21/04/09	Farnell	05/05/09



Specifications:

Electrical Performance:

Impedance : 50Ω .

Frequency range : DC to 3GHz. Maximum working voltage : 60V rms. Minimum dielectric withstanding voltage : 200V rms. Minimum Insulation resistance : $500M\Omega$.

Specification Table

Item	Description	Part Number		
1	RP-SMA B/H Jack Crimp Type for φ1.37mm Cable (Nut x 1, Washer x 1)			
2	Heat Shrink Tube F32 φ2.5mm L = 10.0mm Colour: Black			
3	φ1.37mm Cable Tin Plated Colour: Black	R-134G7210300CB		
4	U.FL-LP-088 Shell for φ1.37mm Cable			
5	U.FL-LP-088 Contact Terminal for φ1.37mm Cable			

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its registered trademark of the Group. © Premier Farnell pic 2009.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

TOLERANCES:

DRAWN BY:	DATE:		
Veena	21/04/09		
CHECKED BY:	DATE:		
Suresh	21/04/09		
Suican			
APPROVED BY:	DATE:		

Cable Assembly - U.FL - SMA, IP67, RP, 300mm

SIZE DWG NO. M10002083 ELECTRONIC FILE REV 1699263-TDS_DWG A

SCALE: NTS U.O.M.: mm

SHEET: 1 OF 1