

CB - CLEAR BRAIDED PVC



TECHNICAL CHARACTERISTICS

SPECIFICATION: N/A

APPLICATION: Ideal for water supply and draining, high resistance to alkalis and acids.

TUBE: PVC




REINFORCEMENT: N/A

COVER: PVC

TEMPERATURE RANGE: 0 degrees C to + 60 degrees C

SAFETY FACTOR: 3:1

BRANDING: N/A

	I.D 	O.D 	W.P 	W.P 	BR 	COIL LENGTH 
Inch	mm	mm	BAR	PSI	mm	mt
3/16"	5	10	20	300	-	30
1/4"	6	11	15	220	-	30
5/16"	8	13	15	220	-	30
3/8"	10	15	12	170	-	30
1/2"	13	18	12	170	-	30
5/8"	16	21	10	150	-	30
3/4"	19	25	10	150	-	30
1"	25	31	9	130	-	30
1 1/4"	32	42	10	150	-	30
1 1/2"	38	48	6	90	-	30
2"	51	60	3	40	-	30