



550A-1 Outdoor Push Button Timer – Three wire IP66

The 550A-1 Outdoor Push Button Timer is part of the Elkay family of switches, timers and detectors which save energy and increase convenience in and around your home or business premises.



Product description

This is an IP66 rated 16A* Outdoor rated electronic time delay switch from the Elkay Illuminated timer family. The 550A-1 Outdoor Push Button Timer to provide energy saving functionality by timing power source off to avoid unnecessary power usage.

This electronic time delay switch requires a firm push of the button to switch the unit ON. The unit will switch OFF after the adjustable time has elapsed. Sixteen variable timing selections are provided ranging from 2 minutes to 2 hours. This product has a firm push to ensure that there is a solid IP66 seal and also to prevent children switching the unit ON. If the end user requires an easier activation, we recommend instead the 560A-1 Elkay Outdoor Touch Timer.

Typical Product usage

The 550A-1 Outdoor Push button timer is commonly used to control all types of external loads from lighting to heating. Applications for suitable use include outdoor patio heaters, lighting such as LED lighting, LED floodlights, fluorescent and compact fluorescent lighting, amenity lighting, pond pumps and waterfalls. This product requires a neutral. The 550A-1 Outdoor Push button timer can be interlinked with any other 3 wire Illuminated Master timers for multi-way switching applications.

Key features

- 16A any load type
- 3 wire (Live, Switch live and Neutral required)
- Blue Locator ring
- Re-set timing sequence at any time during countdown
- Cancellation function with a manual override OFF capability after 1 minute.
- One minute countdown LED indicator
- Can be interlinked with other 3 wire Outdoor masters for 2-way switching.
- IP66 rated outdoor backboxes provided to maintain IP rating which <u>must</u> be used.
- 16 Timer settings from 2 mins to 2 hours
- Recommended connections are with IP rated Cable glands and IP rated SWA glands. It is advisable to
 use nylon sealing washers provided in connections to the box (provided for your convenience).
 Connections should be tight, and a condensation drain hole can be drilled as an option where
 applicable and at the discretion of the installer.







Technical Specification

Voltage: 240V a.c.Frequency: 50/60Hz

• IP rating: IP66

Operating Temperature: -10 to 45 °C

• Timing: 2 minutes to 2 hours

Connections: Live | Switch Live | Neutral |

Loading: Up to 16A all load types*

Marking: CE & UKCA

• Terminal Capacity: 2.5mm²

• **Standards:** BS EN 60669, 60669-1, 60669-2-1, 60669-2-3.

• Power Consumption: 0.65W

Material: Flame Retardant ABS / UV Resistant

• **Compliances:** RoHS compliant, WEEE Policy, ISO9001, ISO14001.

Total Product Weight (each): 265g
 Total Plastic Weight (each): 114.8g

Dimensions –

Front View




Side View



Back Box

This Outdoor Push Button Timer must be used with the back box provided to ensure the IP66 rating. Failure to use this box invalidates the warranty. The timer and back box are a complete unit.



Back Box

Amendments Record

Action	Date
Draft Issue	06/07/2021



^{*}All load type switching means that all load types such as LED, Fluorescent, Compact fluorescent, Resistive and Induction can be switched at 16Amps (3680W) without the need to derate.