

Standard Extraction Tool

Standard design for all new applications

Features:

- Ergonomic Handle design
- Pull-out and lock protection feature



Part Number	Description	mm ² (AWG) or other
5-1579007-3	AMP MCP 1.2	
1452426-1	AMP MCP 1.2 Clean Body	
1-1579007-1	AMP MCP 1.5	
1-1579007-2	AMP MCP 2.8; SENSOR-TAB 2.8	
1-1579007-3	AMP MCP 4.8, 6.3	
166645-1	AMP MODU IV, V	
1579007-9	AMPLIMITE HD 20	
1579007-2	Contact Rail	
1-1579007-5	ECONOSEAL III 070	
5-1579007-4	FFC-MQS	
539764-1	MATE-N-LOK 3.5	
1-1579007-7	Maxi-Power-Timer	
539971-1	Maxi-Power-Timer MCP	
5-1579007-5	MICRO TIMER I	
539960-1	MICRO TIMER II, III, IV; TAB 1.6	
1-1579007-0	MK25/60 - for unlocking 47 way Housing 9-1394129-1	
4-1579007-8	MQS	
6-1579007-0	MQS Clean Body	
3-1579007-6	MW-GET Pin/Socket	
3-1579007-7	Pin Ø1.5	
1-1579007-8	Pin/Socket Ø2.5	
539967-1	Pin/Socket Ø4.0	
1-1579007-6	Standard/Junior Power TIMER; TAB 2.8, 4.8 & 5.8 (symmetric contacts only)	
539972-1	Socket Ø1.5; TYPE II, III+; CI-2, -3, -H	
2-1579007-1	Standard Power Timer - John Deer Housings only	
1-1579007-4	Standard/Junior TIMER; FASTIN-FASTON 2.8, 4.8, 5.8, 6.3	
9-1579007-1	SUPER-SEAL 1.5; MULTILOCK 070	
4-1579007-1	TAB 3.3	
1579008-5	Type F	
9-1579007-5	Universal MATE-N-LOK. Housings: 1-480698-0, 1-480700-0, 1-480704-0, 350720-1, 350779-1	
9-1579007-6	Universal MATE-N-LOK. Housings: 1-480699-0, 1-480705-0	

Extraction Tool

Many designs now superseded by the Standard Extraction Tool

Features:

Many design variants



Part Number	Description	mm ² (AWG) or other
230238-1	AMP CHAMP	
188688-1	AMP DUAC	
465199-1	AMP-BLADE	
465195-1	AMP-LEAF	
726364-2	AMPLIMITE HD 22	
91074-1	Coax T5 & T9	
318831-1	COMM 062	
318837-1	COMM 093	
457241-1	CST	
91302-1	CST 100	
1276716-1	DYNAMIC D2	
234168-1	DYNAMIC D3	
937313-1	E-J Mk II 070	
91232-1	HDE	
753787-1	MIC MK-2	
723735-1	MIC MK-I	
843996-6	MICRO MATE-N-LOK	
843477-1	MTE;SHORT-POINT Receptacle	
1276565-1	MULTILOCK 025	
755430-1	MULTILOCK 040	
90471-1	SL 156	
1102855-3	SOLARLOK	
785084-1	SUPER-SEAL 1.5 (secondary lock of TAB Connector)	

Standard Insertion Tool

Standard design for all new applications

Features:

- Ergonomic Handle design
- Pull-out and lock protection feature



Part Number	Description
1-1579007-9	Pin/Socket Ø4.0

mm² (AWG) or other

Insertion Tool

Many designs now superseded by the Standard Insertion Tool

Features:

- Many design variants



Part Number	Description
726363-1	AMPLIMITE HD 20 DF
726363-2	AMPLIMITE HD 22
455830-1	Mini Universal MATE-N-LOK; Universal MATE-N-LOK
200893-2	TYPE II, III+

mm² (AWG) or other

Tee Handled Insertion Tool

Features:

Comfortable moulded handle
Moulded-in metal insert for long life



Part Number	Description	mm ² (AWG) or other
229384-1	AMP CHAMP Connectors	
91287-1	HDE	
525421-5	HE 13/14	0.08 - 0.22 (28-24)
1-525421-3	IDC Bulb Holder 5 mm	0.2 (24)
525421-6	IDC FASTON	0.2 - 0.4 (22-24)
59803-1	MTA 100	0.08 - 0.4 (28-22)
59804-1	MTA 156	0.15 - 1.0 (26-18)