

SAMSUNG UE32T4300



SCREEN

Screen size 32"
Screen technology LED
Resolution HD Ready 1366 x 768p
HDR Yes

PICTURE QUALITY

Processing rate 900 PQI
Dynamic contrast ratio Mega
Picture enhancement PurColor
HDR game mode Yes
Noise reduction Yes

SMART

Smart platform Samsung Smart Hub
Smart TV services- Catch up TV: BBC iPlayer, ITV Hub, All 4, My5
- Streaming: Netflix, Prime Video, BritBox, Disney+, Rakuten, Apple TV+, NOW TV
- App store: Samsung TV App Store
- Custom homepage
- Full internet browser
- Social media: YouTube, YouTube Kids
- Gaming apps
Screen mirroring Yes
Smartphone app SmartThings
Other smart features Works with Alexa, Bixby & Google Assistant speakers

CONNECTIVITY

WiFi Yes
Ethernet Yes
DLNA certified Yes
Connections- HDMI 2.0a x 2
- USB 2.0 x 1
Audio output Optical x 1

TUNER

TV tuner TV PLUS
Electronic programme guide 7-day EPG
AUDIO
Speakers 2
Audio power 10 W
Sound enhancement Dolby Digital Plus
Supports High-Resolution Audio Yes

FEATURES

PVR function Yes
VESA mount 100 x 100
Table-top stand Yes
Other features Sleep timer

ENERGY CONSUMPTION

Energy efficiency class A+
On-mode power consumption 31 W
Annual power consumption 43 kWh

GENERAL

Colour Black
Material Aluminium & plastic
Internal menu languages 28 languages
Box contents - Samsung UE32T4300AKXXU 32" Smart HD Ready LED TV, Remote control, Batteries, User manual, E-manual, Power cable

Dimensions (H x W x D)

- TV with stand: 465.4 x 737.4 x 150.5 mm
- TV: 438 x 737.4 x 74.1 mm
- Boxed: 500 x 879 x 127 mm

Weight

- TV: 4 kg
- TV with stand: 4.1 kg
- Boxed: 5.8 kg