9070T100D5

Transformer, Type T, industrial control, 100 VA, 550/600/575 VAC pri / 110/120/115 VAC second, 1 phase, 50/60 Hz, 55 °C





Main

Product Type	Industrial Control Transformer	
Power Rating	100 VA	
Туре	Т	

Complementary

100 VA	
55 °C	
Screw clamp terminals	
2.89 in (73.41 mm)	
3.38 in (85.85 mm)	
3.34 in (84.84 mm)	
Copper winding	
FSC1	
	Screw clamp terminals 2.89 in (73.41 mm) 3.38 in (85.85 mm) 3.34 in (84.84 mm) Copper winding

Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239	
Enclosure Type	Not rated (open device)	
Insulation Temperature	221 °F (105 °C)	

Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA	
Discount Schedule	CP8	
GTIN	00785901905370	
Nbr. of units in pkg.	1	
Package weight(Lbs)	3.89 lb(US) (1.76 kg)	
Returnability	Yes	
Country of origin	MX	

Packing Units

Package 1 Height	3.70 in (9.398 cm)	
Package 1 width	4.20 in (10.668 cm)	
Package 1 Length	4.00 in (10.160 cm)	


Offer Sustainability

Sustainable offer status	Green Premium product		
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		
EU RoHS Directive	Compliant E EU RoHS Declaration		
Mercury free	Yes		
RoHS exemption information	₫Yes		
China RoHS Regulation	☐ China RoHS Declaration		
Environmental Disclosure	Product Environmental Profile		
PVC free	Yes		

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions



Connections and Wiring Diagrams

Voltage and Connection Options

Voltage Code	Voltages		Connections	
Voltage Code	Primary	Secondary	Primary	Secondary
D3	208	120	Connect to H1 and H2	Connect to X1 and X2
D4	277	120		
D5	550 575 600	110 115 120		
D6	380	110		
D17	415	110		
D24	110 115 120	110 115 120		
D93	200	115		
D103	400	120		

