



Main

| | |
|---------------------------|---|
| Product or component type | Industrial Control Transformer |
| Power Rating | 750 VA |
| Primary Voltage | 220 x 440 V 240 x 480 V 230 x 460 V |
| Secondary Voltage | 115 V 110 V 120 V |
| Type | TF |

Complementary

| | |
|--------------------------------|---|
| Number of Phases | 1 phase |
| Power Rating | 750 VA UL 750 VA CSA 750 VA NOM 500 VA |
| Primary to Secondary Voltage | 220 x 440 V 110 V 230 x 460 V 115 V 240 x 480 V 120 V |
| Fuse type | 0.41 x 1.50 in CC top |
| Temperature rise | 115 °C |
| Electrical connection | Screw clamp terminals |
| Height | 5.8 in (147.32 mm) |
| Width | 5.25 in (133.35 mm) |
| Depth | 5.61 in (142.49 mm) |
| Material | Copper winding |
| Fingersafe Cover Compatibility | FSC2 |

Environment

| | |
|------------------------|--|
| Product certifications | UL listed file E61239 CSA file LR37055 guide 184-N-90 |
| Enclosure Type | Not rated (open device) |
| Insulation temperature | 356 °F (180 °C) |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 16203 - 9070 TF (NOT T) 250-1000VA |
| Discount Schedule | CP8 |
| GTIN | 00785901904908 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 18.13 lb(US) (8.22 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 7.00 in (17.780 cm) |
| Package 1 width | 8.20 in (20.828 cm) |
| Package 1 Length | 8.70 in (22.098 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|