

Precision Pillar Drill & Machine Vice



- Machined worktop made of high quality, ribbed die-cast aluminium (220 x 120mm)
- Adjustable fence complete with scale
- Solid chrome steel column 280mm high , 20mm diameter
- Stable die- cast head with built in motor
- Three step aluminium pulley with flat belts
- Adjustable depth Gauge
- Triple torque at low speeds
- Supplied with 6 collets 1, 1.5, 2, 2.4, 3, 3.2mm

Technical Data

Power	85W
Voltage	230V
Noise	70dB
Speed	1800 - 8500rpm
Shank Size	3.2mm

494568.478344

Order Code

price each

151-7817